Data Sheet

UBER+SUHNER

RF Attenuator 6820.17.B

Description

Precision Attenuator, Low Power



Product Configuration

Connector (side 1 / side 2) Interface Standards

N-precision plug (male) / N-precision jack (female) IEC 60169-16_MIL-STD-348A/304_CECC 22210

Technical Data

Electrical Data

50 O Nominal impedance 20 dB Nominal attenuation DC to 18 GHz Frequency range

Frequency sub range (GHz) DC to 4 4 to 6 6 to 8 8 to 12.4 12.4 to 18 Attenuation deviation (±dB) 0.6 0.6 8.0 0.5 1 VSWR max. 1.15 1.15 1.25 Power rating 1 Watt average power up to 30 °C ambient temperature, linearly derated to 0 Watt at 130 °C ambient

500 Watt peak power, 5 µs pulse, 0.05 % duty cycle

Mechanical Data

Weight 0.086 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)

-55 °C to 130 °C compliant

Material Data

Piece Part (side 1)	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	Air Dielectric - Bead - PPH	
Coupling nut	Brass	SUCOPLATE (R) Plating
Piece Part (side2)	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer contact	Stainless Steel	
Body	Stainless Steel	
Body	Otalilless Oteel	
Insulator	Air Dielectric - Bead - PPH	

Related Documents

Outline drawing DOU-00005244

Ordering Information

6820.17.B Single packaging

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only