## LM1575,LM2575,LM2575HV

LM1575/LM2575/LM2575HV SIMPLE SWITCHER 1A Step-Down Voltage Regulator



Literature Number: SNVS106D



# LM1575/LM2575/LM2575HV SIMPLE SWITCHER® 1A Step-Down Voltage Regulator

## **General Description**

The LM2575 series of regulators are monolithic integrated circuits that provide all the active functions for a step-down (buck) switching regulator, capable of driving a 1A load with excellent line and load regulation. These devices are available in fixed output voltages of 3.3V, 5V, 12V, 15V, and an adjustable output version.

Requiring a minimum number of external components, these regulators are simple to use and include internal frequency compensation and a fixed-frequency oscillator.

The LM2575 series offers a high-efficiency replacement for popular three-terminal linear regulators. It substantially reduces the size of the heat sink, and in many cases no heat sink is required.

A standard series of inductors optimized for use with the LM2575 are available from several different manufacturers. This feature greatly simplifies the design of switch-mode power supplies.

Other features include a guaranteed  $\pm 4\%$  tolerance on output voltage within specified input voltages and output load conditions, and  $\pm 10\%$  on the oscillator frequency. External shutdown is included, featuring 50  $\mu$ A (typical) standby current. The output switch includes cycle-by-cycle current limiting, as well as thermal shutdown for full protection under fault conditions.

#### **Features**


- 3.3V, 5V, 12V, 15V, and adjustable output versions
- Adjustable version output voltage range,
   1.23V to 37V (57V for HV version) ±4% max over line and load conditions
- Guaranteed 1A output current
- Wide input voltage range, 40V up to 60V for HV version
- Requires only 4 external components
- 52 kHz fixed frequency internal oscillator
- TTL shutdown capability, low power standby mode
- High efficiency
- Uses readily available standard inductors
- Thermal shutdown and current limit protection
- P+ Product Enhancement tested

## **Applications**

- Simple high-efficiency step-down (buck) regulator
- Efficient pre-regulator for linear regulators
- On-card switching regulators
- Positive to negative converter (Buck-Boost)

## **Typical Application**


(Fixed Output Voltage Versions)



Note: Pin numbers are for the TO-220 package.

SIMPLE SWITCHER® is a registered trademark of National Semiconductor Corporation

## **Block Diagram and Typical Application**



3.3V, R2 = 1.7k

5V, R2 = 3.1k

12V, R2 = 8.84k

15V, R2 = 11.3k

For ADJ. Version


 $R1 = Open, R2 = 0\Omega$ 

Note: Pin numbers are for the TO-220 package.


FIGURE 1.


## **Connection Diagrams**


(XX indicates output voltage option. See Ordering Information table for complete part number.)



Top View LM2575T-XX or LM2575HVT-XX See NS Package Number T05A









\*No Internal Connection


Top View LM2575N-XX or LM2575HVN-XX See NS Package Number N16A LM1575J-XX-QML See NS Package Number J16A



\*No Internal Connection

Top View LM2575M-XX or LM2575HVM-XX See NS Package Number M24B







Side View LM2575S-XX or LM2575HVS-XX See NS Package Number TS5B

## **Ordering Information**

Package	NSC	Standard	High	Temperature
Type	Package	Voltage Rating	Voltage Rating	Range
	Number	(40V)	(60V)	
5-Lead TO-220	T05A	LM2575T-3.3	LM2575HVT-3.3	
Straight Leads		LM2575T-5.0	LM2575HVT-5.0	
		LM2575T-12	LM2575HVT-12	
		LM2575T-15	LM2575HVT-15	
		LM2575T-ADJ	LM2575HVT-ADJ	
5-Lead TO-220	T05D	LM2575T-3.3 Flow LB03	LM2575HVT-3.3 Flow LB03	
Bent and		LM2575T-5.0 Flow LB03	LM2575HVT-5.0 Flow LB03	
Staggered Leads		LM2575T-12 Flow LB03	LM2575HVT-12 Flow LB03	
		LM2575T-15 Flow LB03	LM2575HVT-15 Flow LB03	
		LM2575T-ADJ Flow LB03	LM2575HVT-ADJ Flow LB03	
16-Pin Molded	N16A	LM2575N-5.0	LM2575HVN-5.0	-40°C ≤ T <sub>J</sub> ≤ +125°C
DIP		LM2575N-12	LM2575HVN-12	
		LM2575N-15	LM2575HVN-15	
		LM2575N-ADJ	LM2575HVN-ADJ	
24-Pin	M24B	LM2575M-5.0	LM2575HVM-5.0	
Surface Mount		LM2575M-12	LM2575HVM-12	
		LM2575M-15	LM2575HVM-15	
		LM2575M-ADJ	LM2575HVM-ADJ	
5-Lead TO-263	TS5B	LM2575S-3.3	LM2575HVS-3.3	
Surface Mount		LM2575S-5.0	LM2575HVS-5.0	
		LM2575S-12	LM2575HVS-12	
		LM2575S-15	LM2575HVS-15	
		LM2575S-ADJ	LM2575HVS-ADJ	
16-Pin Ceramic	J16A	LM1575J-3.3-QML		
DIP		LM1575J-5.0-QML		
		LM1575J-12-QML		-55°C ≤ T <sub>J</sub> ≤ +150°C
		LM1575J-15-QML		
		LM1575J-ADJ-QML		

2 kV

260°C

## **Absolute Maximum Ratings** (Note 1)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/ Distributors for availability and specifications.

Maximum Supply Voltage

LM1575/LM2575 45V LM2575HV 63V

ON /OFF Pin Input Voltage  $-0.3V \le V \le +V_{IN}$ 

Output Voltage to Ground

(Steady State) **Power Dissipation** Internally Limited

Storage Temperature Range -65°C to +150°C

Maximum Junction Temperature 150°C

Minimum ESD Rating  $(C = 100 pF, R = 1.5 k\Omega)$ 

Lead Temperature

(Soldering, 10 sec.)

## **Operating Ratings**

Temperature Range

LM1575 -55°C ≤ T<sub>1</sub> ≤ +150°C

LM2575/LM2575HV -40°C  $\leq T_{,l} \leq +125$ °C

Supply Voltage

LM1575/LM2575 40V

LM2575HV 60V

#### LM1575-3.3, LM2575-3.3, LM2575HV-3.3 **Electrical Characteristics**

Specifications with standard type face are for T<sub>,I</sub> = 25°C, and those with boldface type apply over full Operating Temperature Range .

Symbol	Parameter	Conditions	Тур	LM1575-3.3	LM2575-3.3 LM2575HV-3.3	Units (Limits)
				Limit	Limit	(=
				(Note 2)	(Note 3)	
SYSTEM	PARAMETERS (Note 4)	Fest Circuit Figure 2				
V <sub>OUT</sub>	Output Voltage	V <sub>IN</sub> = 12V, I <sub>LOAD</sub> = 0.2A	3.3			V
		Circuit of Figure 2		3.267	3.234	V(Min)
				3.333	3.366	V(Max)
V <sub>OUT</sub>	Output Voltage	$4.75V \le V_{IN} \le 40V, 0.2A \le I_{LOAD} \le 1A$	3.3			V
	LM1575/LM2575	Circuit of Figure 2		3.200/ <b>3.168</b>	3.168/ <b>3.135</b>	V(Min)
				3.400/ <b>3.432</b>	3.432/ <b>3.465</b>	V(Max)
V <sub>OUT</sub>	Output Voltage	$4.75V \le V_{IN} \le 60V, 0.2A \le I_{LOAD} \le 1A$	3.3			V
	LM2575HV	Circuit of Figure 2		3.200/ <b>3.168</b>	3.168/ <b>3.135</b>	V(Min)
				3.416/ <b>3.450</b>	3.450/ <b>3.482</b>	V(Max)
η	Efficiency	V <sub>IN</sub> = 12V, I <sub>LOAD</sub> = 1A	75			%

## LM1575-5.0, LM2575-5.0, LM2575HV-5.0 **Electrical Characteristics**

Specifications with standard type face are for T<sub>,I</sub> = 25°C, and those with boldface type apply over full Operating Temperature Range.

Symbol	Parameter	Conditions	Тур	LM1575-5.0	LM2575-5.0 LM2575HV-5.0	Units (Limits)
				Limit	Limit	
				(Note 2)	(Note 3)	
SYSTEM	PARAMETERS (Note 4) 7	est Circuit Figure 2				
V <sub>OUT</sub>	Output Voltage	V <sub>IN</sub> = 12V, I <sub>LOAD</sub> = 0.2A	5.0			V
		Circuit of Figure 2		4.950	4.900	V(Min)
				5.050	5.100	V(Max)
V <sub>OUT</sub>	Output Voltage	$0.2A \le I_{LOAD} \le 1A$ ,	5.0			V
	LM1575/LM2575	8V ≤ V <sub>IN</sub> ≤ 40V		4.850/ <b>4.800</b>	4.800/ <b>4.750</b>	V(Min)
		Circuit of Figure 2		5.150/ <b>5.200</b>	5.200/ <b>5.250</b>	V(Max)

5

Symbol	Parameter	Conditions	Тур	Typ LM1575-5.0 LM2575-		Units (Limits)
				Limit	Limit	
				(Note 2)	(Note 3)	
V <sub>OUT</sub>	Output Voltage	$0.2A \le I_{LOAD} \le 1A$ ,	5.0			V
	LM2575HV	$8V \le V_{IN} \le 60V$		4.850/ <b>4.800</b>	4.800/ <b>4.750</b>	V(Min)
		Circuit of Figure 2		5.175/ <b>5.225</b>	5.225/ <b>5.275</b>	V(Max)
η	Efficiency	$V_{IN} = 12V$ , $I_{LOAD} = 1A$	77			%

## LM1575-12, LM2575-12, LM2575HV-12 Electrical Characteristics

Specifications with standard type face are for  $T_J = 25^{\circ}C$ , and those with **boldface type** apply over **full Operating Temperature Range** .

Symbol	Parameter	eter Conditions Typ		LM1575-12	LM2575-12 LM2575HV-12	Units (Limits)
				Limit	Limit	
				(Note 2)	(Note 3)	
SYSTEM	PARAMETERS (Note 4)	est Circuit Figure 2			•	
V <sub>OUT</sub>	Output Voltage	$V_{IN} = 25V, I_{LOAD} = 0.2A$	12			V
		Circuit of Figure 2		11.88	11.76	V(Min)
				12.12	12.24	V(Max)
V <sub>OUT</sub>	Output Voltage	$0.2A \le I_{LOAD} \le 1A$ ,	12			V
	LM1575/LM2575	$15V \le V_{IN} \le 40V$		11.64/ <b>11.52</b>	11.52/ <b>11.40</b>	V(Min)
		Circuit of Figure 2		12.36/ <b>12.48</b>	12.48/ <b>12.60</b>	V(Max)
V <sub>OUT</sub>	Output Voltage	$0.2A \le I_{LOAD} \le 1A$	12			V
	LM2575HV	15V ≤ V <sub>IN</sub> ≤ 60V		11.64/ <b>11.52</b>	11.52/ <b>11.40</b>	V(Min)
		Circuit of Figure 2		12.42/ <b>12.54</b>	12.54/ <b>12.66</b>	V(Max)
η	Efficiency	V <sub>IN</sub> = 15V, I <sub>LOAD</sub> = 1A	88			%

## LM1575-15, LM2575-15, LM2575HV-15 Electrical Characteristics

Specifications with standard type face are for  $T_J = 25^{\circ}C$ , and those with **boldface type** apply over **full Operating Temperature Range** .

Symbol	Parameter	Conditions	Тур	LM1575-15	LM2575-15 LM2575HV-15	Units (Limits)
				Limit	Limit	
				(Note 2)	(Note 3)	
SYSTEM	PARAMETERS (Note	4) Test Circuit <i>Figure 2</i>	•		,	
V <sub>OUT</sub>	Output Voltage	$V_{IN} = 30V, I_{LOAD} = 0.2A$	15			V
		Circuit of Figure 2		14.85	14.70	V(Min)
				15.15	15.30	V(Max)
V <sub>OUT</sub>	Output Voltage	$0.2A \le I_{LOAD} \le 1A$ ,	15			V
	LM1575/LM2575	18V ≤ V <sub>IN</sub> ≤ 40V		14.55/ <b>14.40</b>	14.40/ <b>14.25</b>	V(Min)
		Circuit of Figure 2		15.45/ <b>15.60</b>	15.60/ <b>15.75</b>	V(Max)
V <sub>OUT</sub>	Output Voltage	$0.2A \le I_{LOAD} \le 1A$	15			V
	LM2575HV	$18V \le V_{IN} \le 60V$		14.55/ <b>14.40</b>	14.40/ <b>14.25</b>	V(Min)
		Circuit of Figure 2		15.525/ <b>15.675</b>	15.68/ <b>15.83</b>	V(Max)
η	Efficiency	V <sub>IN</sub> = 18V, I <sub>LOAD</sub> = 1A	88			%

## LM1575-ADJ, LM2575-ADJ, LM2575HV-ADJ Electrical Characteristics

Specifications with standard type face are for  $T_J$ = 25°C, and those with **boldface type** apply over **full Operating Temperature Range**.

Symbol	Parameter	Conditions	Тур	LM1575-ADJ	LM2575-ADJ LM2575HV-ADJ	Units (Limits)
				Limit	Limit	
				(Note 2)	(Note 3)	
SYSTEM	PARAMETERS (Note 4)	Test Circuit <i>Figure 2</i>				
V <sub>OUT</sub>	Feedback Voltage	$V_{IN} = 12V, I_{LOAD} = 0.2A$	1.230			V
		$V_{OUT} = 5V$		1.217	1.217	V(Min)
		Circuit of Figure 2		1.243	1.243	V(Max)
V <sub>OUT</sub>	Feedback Voltage	$0.2A \le I_{LOAD} \le 1A$ ,	1.230			V
	LM1575/LM2575	$8V \le V_{IN} \le 40V$		1.205/ <b>1.193</b>	1.193/ <b>1.180</b>	V(Min)
		V <sub>OUT</sub> = 5V, Circuit of <i>Figure 2</i>		1.255/ <b>1.267</b>	1.267/ <b>1.280</b>	V(Max)
V <sub>OUT</sub>	Feedback Voltage	$0.2A \le I_{LOAD} \le 1A$ ,	1.230			V
	LM2575HV	8V ≤ V <sub>IN</sub> ≤ 60V		1.205/ <b>1.193</b>	1.193/ <b>1.180</b>	V(Min)
		V <sub>OUT</sub> = 5V, Circuit of Figure 2		1.261/ <b>1.273</b>	1.273/ <b>1.286</b>	V(Max)
η	Efficiency	$V_{IN} = 12V, I_{LOAD} = 1A, V_{OUT} = 5V$	77			%

## All Output Voltage Versions Electrical Characteristics

Specifications with standard type face are for  $T_J = 25^{\circ}\text{C}$ , and those with **boldface type** apply over **full Operating Temperature Range**. Unless otherwise specified,  $V_{IN} = 12\text{V}$  for the 3.3V, 5V, and Adjustable version,  $V_{IN} = 25\text{V}$  for the 12V version, and  $V_{IN} = 30\text{V}$  for the 15V version.  $I_{LOAD} = 200\text{ mA}$ .

Symbol	Parameter	Parameter Conditions		LM1575-XX	LM2575-XX LM2575HV-XX	Units (Limits)
				Limit	Limit	
				(Note 2)	(Note 3)	
DEVICE F	PARAMETERS		<del></del>			
I <sub>b</sub>	Feedback Bias Current	V <sub>OUT</sub> = 5V (Adjustable Version Only)	50	100/ <b>500</b>	100/ <b>500</b>	nA
f <sub>O</sub>	Oscillator Frequency	(Note 13)	52			kHz
				47/ <b>43</b>	47/ <b>42</b>	kHz(Min)
				58/ <b>62</b>	58/ <b>63</b>	kHz(Max)
V <sub>SAT</sub>	Saturation Voltage	I <sub>OUT</sub> = 1A (Note 5)	0.9			V
				1.2/ <b>1.4</b>	1.2/ <b>1.4</b>	V(Max)
DC	Max Duty Cycle (ON)	(Note 6)	98			%
				93	93	%(Min)
I <sub>CL</sub>	Current Limit	Peak Current (Notes 5, 13)	2.2			Α
				1.7/ <b>1.3</b>	1.7/ <b>1.3</b>	A(Min)
				3.0/ <b>3.2</b>	3.0/ <b>3.2</b>	A(Max)
IL	Output Leakage	(Notes 7, 8) Output = 0V		2	2	mA(Max)
	Current	Output = −1V	7.5			mA
		Output = -1V		30	30	mA(Max)
IQ	Quiescent Current	(Note 7)	5			mA
				10/ <b>12</b>	10	mA(Max)
I <sub>STBY</sub>	Standby Quiescent	ON /OFF Pin = 5V (OFF)	50			μA
	Current			200/ <b>500</b>	200	μA(Max)

Symbol	lymbol Parameter Conditions		Тур	LM1575-XX	LM2575-XX LM2575HV-XX	Units (Limits)
				Limit	Limit	
				(Note 2)	(Note 3)	
$\theta_{JA}$	Thermal Resistance	T Package, Junction to Ambient (Note 9)	65			
$\theta_{JA}$		T Package, Junction to Ambient (Note 10)	45			°C/W
$\theta_{JC}$		T Package, Junction to Case	2			
$\theta_{JA}$		N Package, Junction to Ambient (Note 11)	85			
$\theta_{JA}$		M Package, Junction to Ambient (Note 11)	100			
$\theta_{JA}$		S Package, Junction to Ambient (Note 12)	37			
ON /OFF	CONTROL Test Circuit /	igure 2			•	
V <sub>IH</sub>	ON /OFF Pin Logic	$V_{OUT} = 0V$	1.4	2.2/ <b>2.4</b>	2.2/ <b>2.4</b>	V(Min)
V <sub>IL</sub>	Input Level	V <sub>OUT</sub> = Nominal Output Voltage	1.2	1.0/ <b>0.8</b>	1.0/ <b>0.8</b>	V(Max)
I <sub>IH</sub>	ON /OFF Pin Input	ON /OFF Pin = 5V (OFF)	12			μA
	Current			30	30	μA(Max)
I <sub>IL</sub>		ON /OFF Pin = 0V (ON)	0			μΑ
				10	10	μA(Max)

Note 1: Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but do not guarantee specific performance limits. For guaranteed specifications and test conditions, see the Electrical Characteristics.

Note 2: All limits guaranteed at room temperature (standard type face) and at temperature extremes (bold type face). All limits are used to calculate Average Outgoing Quality Level, and all are 100% production tested.

**Note 3:** All limits guaranteed at room temperature (standard type face) and at **temperature extremes (bold type face)**. All room temperature limits are 100% production tested. All limits at **temperature extremes** are guaranteed via correlation using standard Statistical Quality Control (SQC) methods.

**Note 4:** External components such as the catch diode, inductor, input and output capacitors can affect switching regulator system performance. When the LM1575/LM2575 is used as shown in the *Figure 2* test circuit, system performance will be as shown in system parameters section of Electrical Characteristics.

Note 5: Output (pin 2) sourcing current. No diode, inductor or capacitor connected to output pin.

Note 6: Feedback (pin 4) removed from output and connected to 0V.

Note 7: Feedback (pin 4) removed from output and connected to +12V for the Adjustable, 3.3V, and 5V versions, and +25V for the 12V and 15V versions, to force the output transistor OFF.

**Note 8:**  $V_{IN} = 40V$  (60V for the high voltage version).

Note 9: Junction to ambient thermal resistance (no external heat sink) for the 5 lead TO-220 package mounted vertically, with ½ inch leads in a socket, or on a PC board with minimum copper area.

Note 10: Junction to ambient thermal resistance (no external heat sink) for the 5 lead TO-220 package mounted vertically, with ½ inch leads soldered to a PC board containing approximately 4 square inches of copper area surrounding the leads.

Note 11: Junction to ambient thermal resistance with approximately 1 square inch of pc board copper surrounding the leads. Additional copper area will lower thermal resistance further. See thermal model in Switchers made Simple software.


Note 12: If the TO-263 package is used, the thermal resistance can be reduced by increasing the PC board copper area thermally connected to the package: Using 0.5 square inches of copper area,  $\theta_{JA}$  is 50°C/W; with 1 square inch of copper area,  $\theta_{JA}$  is 37°C/W; and with 1.6 or more square inches of copper area,  $\theta_{JA}$  is 32°C/W.

Note 13: The oscillator frequency reduces to approximately 18 kHz in the event of an output short or an overload which causes the regulated output voltage to drop approximately 40% from the nominal output voltage. This self protection feature lowers the average power dissipation of the IC by lowering the minimum duty cycle from 5% down to approximately 2%.


Note 14: Refer to RETS LM1575J for current revision of military RETS/SMD.

## Typical Performance Characteristics (Circuit of Figure 2)


#### **Normalized Output Voltage**




## Line Regulation




#### **Dropout Voltage**




#### **Current Limit**





#### **Quiescent Current**





## Standby

























Maximum Power Dissipation (TO-263) (See (Note 12))





**Load Transient Response** 



 $V_{OUT} = 5V$ 

A: Output Pin Voltage, 10V/div

B: Output Pin Current, 1A/div

C: Inductor Current, 0.5A/div

D: Output Ripple Voltage, 20 mV/div,

AC-Coupled

Horizontal Time Base: 5 µs/div

1147507

Output Voltage

Change


Load Current

## **Test Circuit and Layout Guidelines**

As in any switching regulator, layout is very important. Rapidly switching currents associated with wiring inductance generate voltage transients which can cause problems. For minimal inductance and ground loops, the length of the leads indicated

by heavy lines should be kept as short as possible. Single-point grounding (as indicated) or ground plane construction should be used for best results. When using the Adjustable version, physically locate the programming resistors near the regulator, to keep the sensitive feedback wiring short.

**Fixed Output Voltage Versions** 




 $C_{IN}$  — 100  $\mu F$ , 75V, Aluminum Electrolytic

 $C_{OUT}$  — 330  $\mu$ F, 25V, Aluminum Electrolytic

D1 — Schottky, 11DQ06

 $L1 - 330 \,\mu\text{H}$ , PE-52627 (for 5V in, 3.3V out, use 100  $\mu\text{H}$ , PE-92108)

**Adjustable Output Voltage Version** 



$$V_{OUT} = V_{REF} \left( 1 + \frac{R2}{R1} \right)$$

$$R2 = R1 \left( \frac{V_{OUT}}{V_{REF}} - 1 \right)$$

where  $V_{REF}$  = 1.23V, R1 between 1k and 5k.

R1 — 2k, 0.1%

R2 — 6.12k, 0.1%

Note: Pin numbers are for the TO-220 package.

FIGURE 2.

## LM2575 Series Buck Regulator Design Procedure

times the maximum input voltage.

close to the regulator is needed for stable operation.

4. Input Capacitor (C<sub>IN</sub>)

#### **PROCEDURE (Fixed Output Voltage Versions) EXAMPLE (Fixed Output Voltage Versions)** Given: Given: V<sub>OUT</sub> = Regulated Output Voltage (3.3V, 5V, 12V, or 15V) $V_{OUT} = 5V$ $V_{IN}(Max) = 20V$ V<sub>IN</sub>(Max) = Maximum Input Voltage $I_{LOAD}(Max) = Maximum Load Current$ $I_{LOAD}(Max) = 0.8A$ 1. Inductor Selection (L1) 1. Inductor Selection (L1) A. Select the correct Inductor value selection guide from Figures A. Use the selection guide shown in Figure 4. 3, 4, 5, 6 (Output voltages of 3.3V, 5V, 12V or 15V respectively) B. From the selection guide, the inductance area intersected by For other output voltages, see the design procedure for the adthe 20V line and 0.8A line is L330. justable version. C. Inductor value required is 330 µH. From the table in Figure 9. **B.** From the inductor value selection guide, identify the inductance choose AIE 415-0926, Pulse Engineering PE-52627, or RL1952. region intersected by V<sub>IN</sub>(Max) and I<sub>LOAD</sub>(Max), and note the inductor code for that region. C. Identify the inductor value from the inductor code, and select an appropriate inductor from the table shown in Figure 9. Part numbers are listed for three inductor manufacturers. The inductor chosen must be rated for operation at the LM2575 switching frequency (52 kHz) and for a current rating of $1.15 \times I_{LOAD}$ . For additional inductor information, see the inductor section in the Application Hints section of this data sheet. 2. Output Capacitor Selection (COUT) 2. Output Capacitor Selection (COUT) **A.** The value of the output capacitor together with the inductor de- | **A.** $C_{OUT}$ = 100 $\mu$ F to 470 $\mu$ F standard aluminum electrolytic. fines the dominate pole-pair of the switching regulator loop. For B. Capacitor voltage rating = 20V. stable operation and an acceptable output ripple voltage, (approximately 1% of the output voltage) a value between 100 µF and 470 uF is recommended. B. The capacitor's voltage rating should be at least 1.5 times greater than the output voltage. For a 5V regulator, a rating of at least 8V is appropriate, and a 10V or 15V rating is recommended. Higher voltage electrolytic capacitors generally have lower ESR numbers, and for this reason it may be necessary to select a capacitor rated for a higher voltage than would normally be needed. 3. Catch Diode Selection (D1) 3. Catch Diode Selection (D1) A. The catch-diode current rating must be at least 1.2 times greater A. For this example, a 1A current rating is adequate. than the maximum load current. Also, if the power supply design B. Use a 30V 1N5818 or SR103 Schottky diode, or any of the must withstand a continuous output short, the diode should have a suggested fast-recovery diodes shown in Figure 8. current rating equal to the maximum current limit of the LM2575 The most stressful condition for this diode is an overload or shorted output condition. B. The reverse voltage rating of the diode should be at least 1.25

#### 4. Input Capacitor (CIN)

An aluminum or tantalum electrolytic bypass capacitor located A 47 uF, 25V aluminum electrolytic capacitor located near the input and ground pins provides sufficient bypassing.

## **Inductor Value Selection Guides**

(For Continuous Mode Operation)




FIGURE 3. LM2575(HV)-3.3




FIGURE 4. LM2575(HV)-5.0




FIGURE 5. LM2575(HV)-12




FIGURE 6. LM2575(HV)-15




FIGURE 7. LM2575(HV)-ADJ

#### **PROCEDURE (Adjustable Output Voltage Versions)**

#### Given:

V<sub>OUT</sub> = Regulated Output Voltage

V<sub>IN</sub>(Max) = Maximum Input Voltage

 $I_{LOAD}(Max) = Maximum Load Current$ 

F = Switching Frequency (Fixed at 52 kHz)

1. Programming Output Voltage (Selecting R1 and R2, as shown 1. Programming Output Voltage (Selecting R1 and R2) in Figure 2)

Use the following formula to select the appropriate resistor values.

$$V_{OUT} = V_{REF} \left( 1 + \frac{R2}{R1} \right)$$
 where  $V_{REF} = 1.23V$ 

R<sub>1</sub> can be between 1k and 5k. (For best temperature coefficient and stability with time, use 1% metal film resistors)

$$R2 = R1 \left( \frac{V_{OUT}}{V_{RFF}} - 1 \right)$$

#### 2. Inductor Selection (L1)

A. Calculate the inductor Volt • microsecond constant,

E • T (V • us), from the following formula:

$$\mathsf{E} \bullet \mathsf{T} = (\mathsf{V}_\mathsf{IN} - \mathsf{V}_\mathsf{OUT}) \frac{\mathsf{V}_\mathsf{OUT}}{\mathsf{V}_\mathsf{IN}} \bullet \frac{1000}{\mathsf{F} \, \mathit{(in kHz)}} (\mathsf{V} \bullet \mu \mathsf{s})$$

- B. Use the E T value from the previous formula and match it with the E • T number on the vertical axis of the Inductor Value Selection Guide shown in Figure 7.
- C. On the horizontal axis, select the maximum load current.
- D. Identify the inductance region intersected by the E T value and the maximum load current value, and note the inductor code for that region.
- E. Identify the inductor value from the inductor code, and select an appropriate inductor from the table shown in Figure 9. Part numbers are listed for three inductor manufacturers. The inductor chosen must be rated for operation at the LM2575 switching frequency (52 kHz) and for a current rating of  $1.15 \times I_{LOAD}$ . For additional inductor information, see the inductor section in the application hints section of this data sheet.

#### 3. Output Capacitor Selection (COUT)

A. The value of the output capacitor together with the inductor de- A. fines the dominate pole-pair of the switching regulator loop. For stable operation, the capacitor must satisfy the following requirement:

$$C_{OUT} \ge 7,785 \frac{V_{IN}(Max)}{V_{OUT} \bullet L(\mu H)} (\mu F)$$

The above formula yields capacitor values between 10 µF and 2000 uF that will satisfy the loop requirements for stable operation. But to achieve an acceptable output ripple voltage, (approximately 1% of the output voltage) and transient response, the output capacitor may need to be several times larger than the above formula yields.

B. The capacitor's voltage rating should be at last 1.5 times greater than the output voltage. For a 10V regulator, a rating of at least 15V or more is recommended.

Higher voltage electrolytic capacitors generally have lower ESR numbers, and for this reason it may be necessary to select a capacitor rate for a higher voltage than would normally be needed. (Continued)

#### **EXAMPLE (Adjustable Output Voltage Versions)**

#### Given:

 $V_{OLIT} = 10V$ 

 $V_{IN}(Max) = 25V$ 

 $I_{LOAD}(Max) = 1A$ 

F = 52 kHz

$$V_{OUT} = 1.23 \left( 1 + \frac{R2}{R1} \right) \qquad \text{Select R1} = 1 \text{k}$$

$$R2 = R1 \left( \frac{V_{OUT}}{V_{PEE}} - 1 \right) = 1 \text{k} \left( \frac{10 \text{V}}{1.23 \text{V}} - 1 \right)$$

R2 = 1k (8.13 - 1) = 7.13k, closest 1% value is 7.15k

- 2. Inductor Selection (L1)
- A. Calculate E T (V μs)

$$E \bullet T = (25 - 10) \bullet \frac{10}{25} \bullet \frac{1000}{52} = 115 \text{ V} \bullet \mu\text{s}$$

- **B.**  $E \cdot T = 115 \text{ V} \cdot \mu \text{s}$
- **C.**  $I_{LOAD}(Max) = 1A$
- **D.** Inductance Region = H470
- E. Inductor Value = 470 uH Choose from AIE part #430-0634. Pulse Engineering part #PE-53118, or Renco part #RL-1961.

#### 3. Output Capacitor Selection (COUT)

$$C_{OUT} > 7,785 \frac{25}{10 \cdot 150} = 130 \ \mu F$$

However, for acceptable output ripple voltage select

C<sub>OUT</sub> ≥ 220 µF

 $C_{OLIT}$  = 220 µF electrolytic capacitor

(Continued)

PROCEDURE (Adjustable Output Voltage Versions)	EXAMPLE (Adjustable Output Voltage Versions)
4. Catch Diode Selection (D1)	4. Catch Diode Selection (D1)
A. The catch-diode current rating must be at least 1.2 times greater	
than the maximum load current. Also, if the power supply design must withstand a continuous output short, the diode should have a current rating equal to the maximum current limit of the LM2575. The most stressful condition for this diode is an overload or shorted output. See diode selection guide in <i>Figure 8</i> .	<b>B.</b> Use a 40V MBR340 or 31DQ04 Schottky diode, or any of the suggested fast-recovery diodes in <i>Figure 8</i> .
<b>B.</b> The reverse voltage rating of the diode should be at least 1.25 times the maximum input voltage.	
5. Input Capacitor (C <sub>IN</sub> )	5. Input Capacitor (C <sub>IN</sub> )
An aluminum or tantalum electrolytic bypass capacitor located close to the regulator is needed for stable operation.	A 100 µF aluminum electrolytic capacitor located near the input and ground pins provides sufficient bypassing.

To further simplify the buck regulator design procedure, National Semiconductor is making available computer design software to be used with the Simple Switcher line of switching regulators. **Switchers Made Simple** (version 3.3) is available on a  $(3\frac{1}{2})$  diskette for IBM compatible computers from a National Semiconductor sales office in your area.

V <sub>R</sub>	Sch	ottky	Fast Re	ecovery
	1A	3A	1A	3A
20V	1N5817	1N5820		
	MBR120P	MBR320		
	SR102	SR302		
30V	1N5818	1N5821		
	MBR130P	MBR330	The following	The following
	11DQ03	31DQ03	diodes are all	diodes are all
	SR103	SR303	rated to 100V	rated to 100V
40V	1N5819	IN5822		
	MBR140P	MBR340	11DF1	31DF1
	11DQ04	31DQ04	MUR110	MURD310
	SR104	SR304	HER102	HER302
50V	MBR150	MBR350		
	11DQ05	31DQ05		
	SR105	SR305		
60V	MBR160	MBR360		
	11DQ06	31DQ06		
	SR106	SR306		

FIGURE 8. Diode Selection Guide

Inductor	Inductor	Schott	Pulse Eng.	Renco
Code	Value	(Note 15)	(Note 16)	(Note 17)
L100	100 μH	67127000	PE-92108	RL2444
L150	150 µH	67127010	PE-53113	RL1954
L220	220 µH	67127020	PE-52626	RL1953
L330	330 µH	67127030	PE-52627	RL1952
L470	470 μH	67127040	PE-53114	RL1951
L680	680 µH	67127050	PE-52629	RL1950
H150	150 µH	67127060	PE-53115	RL2445
H220	220 µH	67127070	PE-53116	RL2446
H330	330 µH	67127080	PE-53117	RL2447
H470	470 μH	67127090	PE-53118	RL1961
H680	680 µH	67127100	PE-53119	RL1960
H1000	1000 μH	67127110	PE-53120	RL1959
H1500	1500 µH	67127120	PE-53121	RL1958
H2200	2200 μH	67127130	PE-53122	RL2448

Note 15: Schott Corp., (612) 475-1173, 1000 Parkers Lake Rd., Wayzata, MN 55391.

Note 16: Pulse Engineering, (619) 674-8100, P.O. Box 12236, San Diego, CA 92112.

Note 17: Renco Electronics Inc., (516) 586-5566, 60 Jeffryn Blvd. East, Deer Park, NY 11729.

FIGURE 9. Inductor Selection by Manufacturer's Part Number

## **Application Hints**

#### INPUT CAPACITOR (CIN)

To maintain stability, the regulator input pin must be bypassed with at least a 47  $\mu$ F electrolytic capacitor. The capacitor's leads must be kept short, and located near the regulator.

If the operating temperature range includes temperatures below -25°C, the input capacitor value may need to be larger. With most electrolytic capacitors, the capacitance value decreases and the ESR increases with lower temperatures and age. Paralleling a ceramic or solid tantalum capacitor will increase the regulator stability at cold temperatures. For maximum capacitor operating lifetime, the capacitor's RMS ripple current rating should be greater than

$$\begin{split} &1.2 \times \left(\frac{t_{ON}}{T}\right) \times I_{LOAD} \\ &\text{where } \ \frac{t_{ON}}{T} = \frac{V_{OUT}}{V_{IN}} \text{for a buck regulator} \\ &\text{and } \ \frac{t_{ON}}{T} = \frac{|V_{OUT}|}{|V_{OUT}| + V_{IN}} \text{for a buck-boost regulator.} \end{split}$$

#### INDUCTOR SELECTION

All switching regulators have two basic modes of operation: continuous and discontinuous. The difference between the two types relates to the inductor current, whether it is flowing continuously, or if it drops to zero for a period of time in the normal switching cycle. Each mode has distinctively different operating characteristics, which can affect the regulator performance and requirements.

The LM2575 (or any of the Simple Switcher family) can be used for both continuous and discontinuous modes of operation

The inductor value selection guides in *Figure 3* through *Figure 7* were designed for buck regulator designs of the continuous inductor current type. When using inductor values shown in the inductor selection guide, the peak-to-peak inductor ripple current will be approximately 20% to 30% of the maximum DC current. With relatively heavy load currents, the circuit operates in the continuous mode (inductor current always flowing), but under light load conditions, the circuit will be forced to the discontinuous mode (inductor current falls to zero for a period of time). This discontinuous mode of operation is perfectly acceptable. For light loads (less than approximately 200 mA) it may be desirable to operate the regulator in the discontinuous mode, primarily because of the lower inductor values required for the discontinuous mode.

The selection guide chooses inductor values suitable for continuous mode operation, but if the inductor value chosen is prohibitively high, the designer should investigate the possibility of discontinuous operation. The computer design software *Switchers Made Simple* will provide all component values for discontinuous (as well as continuous) mode of operation.

Inductors are available in different styles such as pot core, toriod, E-frame, bobbin core, etc., as well as different core materials, such as ferrites and powdered iron. The least expensive, the bobbin core type, consists of wire wrapped on a ferrite rod core. This type of construction makes for an inexpensive inductor, but since the magnetic flux is not completely contained within the core, it generates more electromagnetic interference (EMI). This EMI can cause problems in sensitive

circuits, or can give incorrect scope readings because of induced voltages in the scope probe.

The inductors listed in the selection chart include ferrite pot core construction for AIE, powdered iron toroid for Pulse Engineering, and ferrite bobbin core for Renco.

An inductor should not be operated beyond its maximum rated current because it may saturate. When an inductor begins to saturate, the inductance decreases rapidly and the inductor begins to look mainly resistive (the DC resistance of the winding). This will cause the switch current to rise very rapidly. Different inductor types have different saturation characteristics, and this should be kept in mind when selecting an inductor.

The inductor manufacturer's data sheets include current and energy limits to avoid inductor saturation.

#### INDUCTOR RIPPLE CURRENT

When the switcher is operating in the continuous mode, the inductor current waveform ranges from a triangular to a sawtooth type of waveform (depending on the input voltage). For a given input voltage and output voltage, the peak-to-peak amplitude of this inductor current waveform remains constant. As the load current rises or falls, the entire sawtooth current waveform also rises or falls. The average DC value of this waveform is equal to the DC load current (in the buck regulator configuration).

If the load current drops to a low enough level, the bottom of the sawtooth current waveform will reach zero, and the switcher will change to a discontinuous mode of operation. This is a perfectly acceptable mode of operation. Any buck switching regulator (no matter how large the inductor value is) will be forced to run discontinuous if the load current is light enough.

#### **OUTPUT CAPACITOR**

An output capacitor is required to filter the output voltage and is needed for loop stability. The capacitor should be located near the LM2575 using short pc board traces. Standard aluminum electrolytics are usually adequate, but low ESR types are recommended for low output ripple voltage and good stability. The ESR of a capacitor depends on many factors, some which are: the value, the voltage rating, physical size and the type of construction. In general, low value or low voltage (less than 12V) electrolytic capacitors usually have higher ESR numbers.

The amount of output ripple voltage is primarily a function of the ESR (Equivalent Series Resistance) of the output capacitor and the amplitude of the inductor ripple current ( $\Delta I_{IND}$ ). See the section on inductor ripple current in Application Hints. The lower capacitor values (220  $\mu F$ –680  $\mu F$ ) will allow typically 50 mV to 150 mV of output ripple voltage, while larger-value capacitors will reduce the ripple to approximately 20 mV to 50 mV.

Output Ripple Voltage = 
$$(\Delta I_{IND})$$
 (ESR of  $C_{OUT}$ )

To further reduce the output ripple voltage, several standard electrolytic capacitors may be paralleled, or a higher-grade capacitor may be used. Such capacitors are often called "high-frequency," "low-inductance," or "low-ESR." These will reduce the output ripple to 10 mV or 20 mV. However, when operating in the continuous mode, reducing the ESR below  $0.05\Omega$  can cause instability in the regulator.

Tantalum capacitors can have a very low ESR, and should be carefully evaluated if it is the only output capacitor. Because of their good low temperature characteristics, a tantalum can

be used in parallel with aluminum electrolytics, with the tantalum making up 10% or 20% of the total capacitance.

The capacitor's ripple current rating at 52 kHz should be at least 50% higher than the peak-to-peak inductor ripple current.

#### **CATCH DIODE**

Buck regulators require a diode to provide a return path for the inductor current when the switch is off. This diode should be located close to the LM2575 using short leads and short printed circuit traces.

Because of their fast switching speed and low forward voltage drop, Schottky diodes provide the best efficiency, especially in low output voltage switching regulators (less than 5V). Fast-Recovery, High-Efficiency, or Ultra-Fast Recovery diodes are also suitable, but some types with an abrupt turn-off characteristic may cause instability and EMI problems. A fast-recovery diode with soft recovery characteristics is a better choice. Standard 60 Hz diodes (e.g., 1N4001 or 1N5400, etc.) are also **not suitable.** See *Figure 8* for Schottky and "soft" fast-recovery diode selection guide.

#### **OUTPUT VOLTAGE RIPPLE AND TRANSIENTS**

The output voltage of a switching power supply will contain a sawtooth ripple voltage at the switcher frequency, typically about 1% of the output voltage, and may also contain short voltage spikes at the peaks of the sawtooth waveform.

The output ripple voltage is due mainly to the inductor sawtooth ripple current multiplied by the ESR of the output capacitor. (See the inductor selection in the application hints.)

The voltage spikes are present because of the fast switching action of the output switch, and the parasitic inductance of the output filter capacitor. To minimize these voltage spikes, special low inductance capacitors can be used, and their lead lengths must be kept short. Wiring inductance, stray capacitance, as well as the scope probe used to evaluate these transients, all contribute to the amplitude of these spikes.

An additional small LC filter (20  $\mu$ H & 100  $\mu$ F) can be added to the output (as shown in *Figure 15*) to further reduce the amount of output ripple and transients. A 10  $\times$  reduction in output ripple voltage and transients is possible with this filter.

#### **FEEDBACK CONNECTION**

The LM2575 (fixed voltage versions) feedback pin must be wired to the output voltage point of the switching power supply. When using the adjustable version, physically locate both output voltage programming resistors near the LM2575 to avoid picking up unwanted noise. Avoid using resistors greater than  $100~\mbox{k}\Omega$  because of the increased chance of noise pickup.

#### **ON /OFF INPUT**

For normal operation, the  $\overline{ON}$  /OFF pin should be grounded or driven with a low-level TTL voltage (typically below 1.6V). To put the regulator into standby mode, drive this pin with a high-level TTL or CMOS signal. The  $\overline{ON}$  /OFF pin can be safely pulled up to +V $_{IN}$  without a resistor in series with it. The  $\overline{ON}$  /OFF pin should not be left open.

#### GROUNDING

To maintain output voltage stability, the power ground connections must be low-impedance (see *Figure 2*). For the TO-3 style package, the case is ground. For the 5-lead TO-220 style package, both the tab and pin 3 are ground and either connection may be used, as they are both part of the same copper lead frame.

With the N or M packages, all the pins labeled ground, power ground, or signal ground should be soldered directly to wide printed circuit board copper traces. This assures both low inductance connections and good thermal properties.

#### **HEAT SINK/THERMAL CONSIDERATIONS**

In many cases, no heat sink is required to keep the LM2575 junction temperature within the allowed operating range. For each application, to determine whether or not a heat sink will be required, the following must be identified:

- 1. Maximum ambient temperature (in the application).
- 2. Maximum regulator power dissipation (in application).
- Maximum allowed junction temperature (150°C for the LM1575 or 125°C for the LM2575). For a safe, conservative design, a temperature approximately 15°C cooler than the maximum temperature should be selected.
- 4. LM2575 package thermal resistances  $\theta_{JA}$  and  $\theta_{JC}$ . Total power dissipated by the LM2575 can be estimated as follows:

$$\mathsf{P}_\mathsf{D} = (\mathsf{V}_\mathsf{IN}) \; (\mathsf{I}_\mathsf{Q}) + (\mathsf{V}_\mathsf{O}/\mathsf{V}_\mathsf{IN}) \; (\mathsf{I}_\mathsf{LOAD}) \; (\mathsf{V}_\mathsf{SAT})$$

where  $\rm I_Q$  (quiescent current) and  $\rm V_{SAT}$  can be found in the Characteristic Curves shown previously,  $\rm V_{IN}$  is the applied minimum input voltage,  $\rm V_O$  is the regulated output voltage, and  $\rm I_{LOAD}$  is the load current. The dynamic losses during turnon and turn-off are negligible if a Schottky type catch diode is used.

When no heat sink is used, the junction temperature rise can be determined by the following:

$$\Delta T_J = (P_D) (\theta_{JA})$$

To arrive at the actual operating junction temperature, add the junction temperature rise to the maximum ambient temperature.

$$T_J = \Delta T_J + T_A$$

If the actual operating junction temperature is greater than the selected safe operating junction temperature determined in step 3, then a heat sink is required.

When using a heat sink, the junction temperature rise can be determined by the following:

$$\Delta T_J = (P_D) (\theta_{JC} + \theta_{interface} + \theta_{Heat sink})$$

The operating junction temperature will be:

$$T_J = T_A + \Delta T_J$$

As above, if the actual operating junction temperature is greater than the selected safe operating junction temperature, then a larger heat sink is required (one that has a lower thermal resistance).

When using the LM2575 in the plastic DIP (N) or surface mount (M) packages, several items about the thermal properties of the packages should be understood. The majority of the heat is conducted out of the package through the leads, with a minor portion through the plastic parts of the package. Since the lead frame is solid copper, heat from the die is readily conducted through the leads to the printed circuit board copper, which is acting as a heat sink.

For best thermal performance, the ground pins and all the unconnected pins should be soldered to generous amounts of printed circuit board copper, such as a ground plane. Large areas of copper provide the best transfer of heat to the surrounding air. Copper on both sides of the board is also helpful in getting the heat away from the package, even if there is no direct copper contact between the two sides. Thermal resis-

tance numbers as low as 40°C/W for the SO package, and 30°C/W for the N package can be realized with a carefully engineered pc board.

Included on the *Switchers Made Simple* design software is a more precise (non-linear) thermal model that can be used to determine junction temperature with different input-output parameters or different component values. It can also calculate the heat sink thermal resistance required to maintain the regulators junction temperature below the maximum operating temperature.

### **Additional Applications**

#### **INVERTING REGULATOR**

Figure 10 shows a LM2575-12 in a buck-boost configuration to generate a negative 12V output from a positive input voltage. This circuit bootstraps the regulator's ground pin to the negative output voltage, then by grounding the feedback pin, the regulator senses the inverted output voltage and regulates it to -12V.

For an input voltage of 12V or more, the maximum available output current in this configuration is approximately 0.35A. At lighter loads, the minimum input voltage required drops to approximately 4.7V.

The switch currents in this buck-boost configuration are higher than in the standard buck-mode design, thus lowering the available output current. Also, the start-up input current of the buck-boost converter is higher than the standard buck-mode regulator, and this may overload an input power source with a current limit less than 1.5A. Using a delayed turn-on or an undervoltage lockout circuit (described in the next section)

would allow the input voltage to rise to a high enough level before the switcher would be allowed to turn on.

Because of the structural differences between the buck and the buck-boost regulator topologies, the buck regulator design procedure section can not be used to select the inductor or the output capacitor. The recommended range of inductor values for the buck-boost design is between 68  $\mu$ H and 220  $\mu$ H, and the output capacitor values must be larger than what is normally required for buck designs. Low input voltages or high output currents require a large value output capacitor (in the thousands of micro Farads).

The peak inductor current, which is the same as the peak switch current, can be calculated from the following formula:

$$I_{p} \approx \frac{I_{LOAD}\left(V_{IN} + \left|V_{O}\right|\right)}{V_{IN}} + \frac{V_{IN}\left|V_{O}\right|}{V_{IN} + \left|V_{O}\right|} \times \frac{1}{2\,L_{1}\,f_{osc}}$$

Where  $\rm f_{osc}$  = 52 kHz. Under normal continuous inductor current operating conditions, the minimum  $\rm V_{IN}$  represents the worst case. Select an inductor that is rated for the peak current anticipated.

Also, the maximum voltage appearing across the regulator is the absolute sum of the input and output voltage. For a –12V output, the maximum input voltage for the LM2575 is +28V, or +48V for the LM2575HV.

The *Switchers Made Simple* (version 3.3) design software can be used to determine the feasibility of regulator designs using different topologies, different input-output parameters, different components, etc.





FIGURE 10. Inverting Buck-Boost Develops -12V

#### **NEGATIVE BOOST REGULATOR**

Another variation on the buck-boost topology is the negative boost configuration. The circuit in *Figure 11* accepts an input voltage ranging from –5V to –12V and provides a regulated –12V output. Input voltages greater than –12V will cause the output to rise above –12V, but will not damage the regulator. Because of the boosting function of this type of regulator, the switch current is relatively high, especially at low input voltages. Output load current limitations are a result of the maximum current rating of the switch. Also, boost regulators can not provide current limiting load protection in the event of a shorted load, so some other means (such as a fuse) may be necessary.



Typical Load Current 200 mA for  $V_{IN} = -5.2V$ 500 mA for  $V_{IN} = -7V$ 

Note: Pin numbers are for TO-220 package.

**FIGURE 11. Negative Boost** 

#### UNDERVOLTAGE LOCKOUT

In some applications it is desirable to keep the regulator off until the input voltage reaches a certain threshold. An undervoltage lockout circuit which accomplishes this task is shown in *Figure 12*, while *Figure 13* shows the same circuit applied to a buck-boost configuration. These circuits keep the regulator off until the input voltage reaches a predetermined level.


$$V_{TH} V_{Z1} + 2V_{BE} (Q1)$$

#### **DELAYED STARTUP**

The  $\overline{ON}$  /OFF pin can be used to provide a delayed startup feature as shown in *Figure 14*. With an input voltage of 20V and for the part values shown, the circuit provides approximately 10 ms of delay time before the circuit begins switching. Increasing the RC time constant can provide longer delay times. But excessively large RC time constants can cause problems with input voltages that are high in 60 Hz or 120 Hz ripple, by coupling the ripple into the  $\overline{ON}$  /OFF pin.

## ADJUSTABLE OUTPUT, LOW-RIPPLE POWER SUPPLY


A 1A power supply that features an adjustable output voltage is shown in *Figure 15*. An additional L-C filter that reduces the output ripple by a factor of 10 or more is included in this circuit.



Note: Complete circuit not shown.

Note: Pin numbers are for the TO-220 package.


#### FIGURE 12. Undervoltage Lockout for Buck Circuit



Note: Complete circuit not shown (see Figure 10).

Note: Pin numbers are for the TO-220 package.


FIGURE 13. Undervoltage Lockout for Buck-Boost Circuit



Note: Complete circuit not shown.

Note: Pin numbers are for the TO-220 package.

FIGURE 14. Delayed Startup



Note: Pin numbers are for the TO-220 package.

FIGURE 15. 1.2V to 55V Adjustable 1A Power Supply with Low Output Ripple

### **Definition of Terms**

#### **BUCK REGULATOR**

A switching regulator topology in which a higher voltage is converted to a lower voltage. Also known as a step-down switching regulator.

#### **BUCK-BOOST REGULATOR**

A switching regulator topology in which a positive voltage is converted to a negative voltage without a transformer.

#### **DUTY CYCLE (D)**

Ratio of the output switch's on-time to the oscillator period.

$$\label{eq:definition} \text{for buck regulator} \qquad D = \frac{t_{ON}}{T} = \frac{V_{OUT}}{V_{IN}}$$

$$\textit{for buck-boost regulator} \quad D = \frac{t_{ON}}{T} = \frac{|V_O|}{|V_O| + |V_{IN}|}$$

#### **CATCH DIODE OR CURRENT STEERING DIODE**

The diode which provides a return path for the load current when the LM2575 switch is OFF.

#### EFFICIENCY (n)

The proportion of input power actually delivered to the load.

$$\eta = \frac{P_{OUT}}{P_{IN}} = \frac{P_{OUT}}{P_{OUT} + P_{LOSS}}$$

#### **CAPACITOR EQUIVALENT SERIES RESISTANCE (ESR)**

The purely resistive component of a real capacitor's impedance (see *Figure 16*). It causes power loss resulting in capacitor heating, which directly affects the capacitor's operating lifetime. When used as a switching regulator output filter, higher ESR values result in higher output ripple voltages.




FIGURE 16. Simple Model of a Real Capacitor

Most standard aluminum electrolytic capacitors in the 100  $\mu\text{F}$  –1000  $\mu\text{F}$  range have  $0.5\Omega$  to  $0.1\Omega$  ESR. Higher-grade capacitors ("low-ESR", "high-frequency", or "low-inductance") in the 100  $\mu\text{F}$  –1000  $\mu\text{F}$  range generally have ESR of less than  $0.15\Omega$ .

#### **EQUIVALENT SERIES INDUCTANCE (ESL)**

The pure inductance component of a capacitor (see *Figure 16*). The amount of inductance is determined to a large extent on the capacitor's construction. In a buck regulator, this unwanted inductance causes voltage spikes to appear on the output.

#### **OUTPUT RIPPLE VOLTAGE**

The AC component of the switching regulator's output voltage. It is usually dominated by the output capacitor's ESR multiplied by the inductor's ripple current ( $\Delta I_{IND}$ ). The peak-to-peak value of this sawtooth ripple current can be determined by reading the Inductor Ripple Current section of the Application hints.

#### **CAPACITOR RIPPLE CURRENT**

RMS value of the maximum allowable alternating current at which a capacitor can be operated continuously at a specified temperature.

#### STANDBY QUIESCENT CURRENT (ISTRY)

Supply current required by the LM2575 when in the standby mode  $(\overline{ON}/OFF$  pin is driven to TTL-high voltage, thus turning the output switch OFF).

#### INDUCTOR RIPPLE CURRENT (ΔI<sub>IND</sub>)

The peak-to-peak value of the inductor current waveform, typically a sawtooth waveform when the regulator is operating in the continuous mode (vs. discontinuous mode).

#### CONTINUOUS/DISCONTINUOUS MODE OPERATION

Relates to the inductor current. In the continuous mode, the inductor current is always flowing and never drops to zero, vs. the discontinuous mode, where the inductor current drops to zero for a period of time in the normal switching cycle.


#### **INDUCTOR SATURATION**

The condition which exists when an inductor cannot hold any more magnetic flux. When an inductor saturates, the inductor appears less inductive and the resistive component dominates. Inductor current is then limited only by the DC resistance of the wire and the available source current.


#### OPERATING VOLT MICROSECOND CONSTANT (E•Top)

The product (in Volt•µs) of the voltage applied to the inductor and the time the voltage is applied. This E•T<sub>op</sub> constant is a measure of the energy handling capability of an inductor and is dependent upon the type of core, the core area, the number of turns, and the duty cycle.


## Physical Dimensions inches (millimeters) unless otherwise noted




16-Lead Ceramic Dual-in-Line (J) Order Number LM1575J-3.3/883, LM1575J-5.0/883, LM1575J-12/883, LM1575J-15/883, or LM1575J-ADJ/883 NS Package Number J16A




24-Lead Wide Surface Mount (WM)
Order Number LM2575M-5.0, LM2575HVM-5.0, LM2575M-12,
LM2575HVM-12, LM2575M-15, LM2575HVM-15,
LM2575M-ADJ or LM2575HVM-ADJ
NS Package Number M24B




16-Lead Molded DIP (N)
Order Number LM2575N-5.0, LM2575HVN-5.0, LM2575N-12, LM2575HVN-12,
LM2575N-15, LM2575HVN-15, LM2575N-ADJ or LM2575HVN-ADJ
NS Package Number N16A



5-Lead TO-220 (T)
Order Number LM2575T-3.3, LM2575HVT-3.3, LM2575T-5.0, LM2575HVT-5.0, LM2575T-12, LM2575HVT-12, LM2575T-15, LM2575HVT-15, LM2575T-ADJ or LM2575HVT-ADJ
NS Package Number T05A



TO-263, Molded, 5-Lead Surface Mount
Order Number LM2575S-3.3, LM2575HVS-3.3, LM2575S-5.0, LM2575HVS-5.0, LM2575S-12,
LM2575HVS-12, LM2575S-15, LM2575HVS-15, LM2575S-ADJ or LM2575HVS-ADJ
NS Package Number TS5B



17.88
Bent, Staggered 5-Lead TO-220 (T)
Order Number LM2575T-3.3 Flow LB03, LM2575HVT-3.3 Flow LB03, LM2575T-5.0 Flow LB03, LM2575HVT-5.0 Flow LB03, LM2575T-12 Flow LB03, LM2575HVT-12 Flow LB03, LM2575T-15 Flow LB03, LM2575HVT-15 Flow LB03, LM2575T-ADJ Flow LB03 or LM2575HVT-ADJ Flow LB03 NS Package Number T05D

## **Notes**

THE CONTENTS OF THIS DOCUMENT ARE PROVIDED IN CONNECTION WITH NATIONAL SEMICONDUCTOR CORPORATION ("NATIONAL") PRODUCTS. NATIONAL MAKES NO REPRESENTATIONS OR WARRANTIES WITH RESPECT TO THE ACCURACY OR COMPLETENESS OF THE CONTENTS OF THIS PUBLICATION AND RESERVES THE RIGHT TO MAKE CHANGES TO SPECIFICATIONS AND PRODUCT DESCRIPTIONS AT ANY TIME WITHOUT NOTICE. NO LICENSE, WHETHER EXPRESS, IMPLIED, ARISING BY ESTOPPEL OR OTHERWISE, TO ANY INTELLECTUAL PROPERTY RIGHTS IS GRANTED BY THIS DOCUMENT.

TESTING AND OTHER QUALITY CONTROLS ARE USED TO THE EXTENT NATIONAL DEEMS NECESSARY TO SUPPORT NATIONAL'S PRODUCT WARRANTY. EXCEPT WHERE MANDATED BY GOVERNMENT REQUIREMENTS, TESTING OF ALL PARAMETERS OF EACH PRODUCT IS NOT NECESSARILY PERFORMED. NATIONAL ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR BUYER PRODUCT DESIGN. BUYERS ARE RESPONSIBLE FOR THEIR PRODUCTS AND APPLICATIONS USING NATIONAL COMPONENTS. PRIOR TO USING OR DISTRIBUTING ANY PRODUCTS THAT INCLUDE NATIONAL COMPONENTS, BUYERS SHOULD PROVIDE ADEQUATE DESIGN, TESTING AND OPERATING SAFEGUARDS.

EXCEPT AS PROVIDED IN NATIONAL'S TERMS AND CONDITIONS OF SALE FOR SUCH PRODUCTS, NATIONAL ASSUMES NO LIABILITY WHATSOEVER, AND NATIONAL DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY RELATING TO THE SALE AND/OR USE OF NATIONAL PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

#### LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS PRIOR WRITTEN APPROVAL OF THE CHIEF EXECUTIVE OFFICER AND GENERAL COUNSEL OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

Life support devices or systems are devices which (a) are intended for surgical implant into the body, or (b) support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in a significant injury to the user. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system or to affect its safety or effectiveness.

National Semiconductor and the National Semiconductor logo are registered trademarks of National Semiconductor Corporation. All other brand or product names may be trademarks or registered trademarks of their respective holders.

Copyright© 2007 National Semiconductor Corporation

For the most current product information visit us at www.national.com



National Semiconductor Americas Customer Support Center Email: new.feedback@nsc.com Tel: 1-800-272-9959 National Semiconductor Europe Customer Support Center Fax: +49 (0) 180-530-85-86 Email: europe.support@nsc.com Deutsch Tel: +49 (0) 69 9508 6208 English Tel: +49 (0) 870 24 0 2171 Français Tel: +33 (0) 1 41 91 8790 National Semiconductor Asia Pacific Customer Support Center Email: ap.support@nsc.com National Semiconductor Japan Customer Support Center Fax: 81-3-5639-7507 Email: jpn.feedback@nsc.com Tel: 81-3-5639-7560

#### IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

## Products Applications

Audio www.ti.com/audio Communications and Telecom www.ti.com/communications **Amplifiers** amplifier.ti.com Computers and Peripherals www.ti.com/computers dataconverter.ti.com Consumer Electronics www.ti.com/consumer-apps **Data Converters DLP® Products** www.dlp.com **Energy and Lighting** www.ti.com/energy DSP dsp.ti.com Industrial www.ti.com/industrial Clocks and Timers www.ti.com/clocks Medical www.ti.com/medical

Interface interface.ti.com Security www.ti.com/security

Logic Space, Avionics and Defense www.ti.com/space-avionics-defense

Power Mgmt power.ti.com Transportation and Automotive www.ti.com/automotive
Microcontrollers Microcontroller.ti.com Video and Imaging www.ti.com/video

RFID <u>www.ti-rfid.com</u>
OMAP Mobile Processors www.ti.com/omap

Wireless Connectivity www.ti.com/wirelessconnectivity

TI E2E Community Home Page <u>e2e.ti.com</u>