

drilling hand vices

Mechanical clamping system

ORION[®]

Application:

Secure clamping and fixing of workpieces on drills and measuring machines

Execution:

- Basic body made of grey cast iron
- Universal means of attachment thanks to clamping slots and slotted holes
- Fixed clamping jaws with vee blocks
- Both jaws with step for clamping flat workpieces
- Black oxide-coated jaws and spindle

Delivery:

1 pc. Handheld drill vice



Art. no.	28660 100
Brand	ORION
Manufacturer Part Number	28660100
Jaws width	100 mm
Clamping width	92 mm
Jaws height	30 mm
Body length	150 mm
Body width	150 mm
Max. length	170 mm
Height	65 mm
Chip flute width	14 mm
Weight	4.6 kg
Gross Weight	4.605 kg
Product Group	282

EAN

4039247171149