



EMI Filters > IEC Unfiltered Inlets > CORCOM SR SERIES IEC UNFILTERED INLETS



Filter Current Rating: **15 A**

Input Connector Type: **IEC 60320/C-13**

Input Connector Style: **Female Receptacle**

Filter Output Termination Type: **1/4" Faston**

Voltage Rating (Max): **250 VAC**

[All CORCOM SR SERIES IEC UNFILTERED INLETS \(7\)](#)

Features

Product Type Features

Input Connector Type	IEC 60320/C-13
Input Connector Style	Female Receptacle
Filter Output Termination Type	1/4" Faston

Electrical Characteristics

Filter Current Rating	15 A
Voltage Rating (Max)	250 VAC

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # CAT-C8114-102
CORCOM C SERIES MULTI-FUNCTION INLET FIL



TE Part # 1-1609112-4
15CBE1=F8274




TE Part # 1609142-1
GA400 POWER LINE CO=F6946

Also in the Series | Corcom SR



IEC Unfiltered Inlets(7)



Multi-Function Inlet Filters(3)

Customers Also Bought



TE Part #1-6609036-4
CORCOM SK SERIES SINGLE PHASE FILTERS



TE Part #1-6609028-3
10VK1=F7143 S0




TE Part #1-1630027-2
HSC300 33R 5%



TE Part #9-1393117-9
KUP-14A55-120=KU



TE Part #1-1609112-2
15CE1=F8272



TE Part #1-640509-0
04P MR II CAP HSG V0 RED



TE Part #1-1546306-2
12P.374 DR BARRIER STRIP

Documents

Product Drawings

[6ESRF-3=F6988](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1609133-1_A.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1609133-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1609133-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE](#)

English

[1654001_CORCOM_PRODUCT_GUIDE_SR_SERIES](#)

English

[Corcom Combined Selector Charts](#)

English

[8-1773460-7_CORCOM_SR_SERIES_FILTERS](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Agency Approvals

[VDE Certificate](#)

English

