

SUBITO KT internal precision measuring instrument

For internal toothing



Application:

For measuring the pitch circle diameter of internal toothing with an odd or even number of teeth, with straight or slanted tooth shapes such as involute toothing.

Execution:

- Graduated, interchangeable gauge slides, with female thread for accommodating measuring ball inserts (not included in the scope of delivery)

Delivery:

Device holder with movable probe bolt, replaceable gauge slides, measuring discs, wooden box. **Ball measuring inserts not included***. Probe bolt and gauge slides with female thread for screwing in ball measuring inserts



Art. no.	33572 022
Brand	SCHWENK
Manufacturer Part Number	16200000
Min./max. diameter of measuring range	22-55 mm
Type	KT
Measuring depth	110 mm
Number of measurement heads	1
Number of measuring pins	9
Nominal dimension of spindle	22 mm, 24 mm, 26 mm, 28 mm, 30 mm, 32 mm, 34 mm, 36 mm, 38 mm
Number of measurement discs	2
Measurement disc thickness	0.5 mm, 1 mm
Gross Weight	0.612 kg
Product Group	338