

# tesa® Professional 74662 STRONG Duct tape



## Product Information

### Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

#### Technical Data

• Backing material	PE-film with PET-filament	• Tensile strength	40 N/cm
• Total thickness	215 µm	• Temperature resistance max.	60 °C
• Type of adhesive	synthetic rubber	• Mesh	27 count per square inch
• Elongation at break	19 %	• Unwind force	2 N/cm

#### Adhesion to

• steel	8.0 N/cm	• rough surfaces	6.5 N/cm
---------	----------	------------------	----------

#### Properties

• Hand tearability	●●●●	• Tack	●●●●
• Straight tear edges	●●●	• Abrasion resistance	●●●
• Easy to remove	no	• Water resistant	●●●
• Easy to write on	no		

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

## Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit  
<http://l.tesa.com/?ip=74662>