

Wichtel belt sanding machine



Application:

The belt sanding machine for horizontal and vertical grinding. Equipped with S1 motors for 100% switch-on time. The capacity of S1 motors is 40% higher compared to S6 motors.

Version:

- sliding belt cover
- S1 three-phase motor 400 V, 50 Hz
- for surface and contact grinding
- low-vibration
- Connection for suction system
- with emergency stop switch
- can be used horizontally and vertically

Delivery:

1 sanding belt and connection cable for optional fixed connection or CEE plug.



Art. no.	78236 110
Model	100/1
Max. sanding belt width	100 mm
Grinding belt length	1000 mm
Max. belt speed	19 m/s
Motor speed	2800 rpm
Motor output	0.75 kW
Weight	38 kg

EAN-Code

4251770603342