

SCLC boring bar, offset, steel, positive, right-hand

For face and longitudinal turning with CC indexable insert

ATORN[®]

Application


For face and longitudinal turning with CC indexable insert 80°.

Version

- Precision-made boring bar, **steel**, with internal cooling, offset, type C, attack angle 95°, tip angle 80°, clearance angle 7°

Advantage

- Universal use for face and longitudinal turning
- Positive body geometry ensures low cutting forces



Art. No.	17846 172
ISO name	A 1012 K SCLC R/L 06
Min. bore diameter	14 mm
Tapered diameter	10 mm
Shaft diameter	12 mm
Clearance length	38 mm
Length	125 mm
Clamping surface height	11 mm
Programming size	7 mm
Suitable for indexable inserts	CC.. 06..
Tool design	Right
DIN	8024

EAN-Code

4050293110319