



THE PHOENIX ELARA HS3550 SERIES are designed to provide extreme security protection for domestic and business use.

- **SECURITY PROTECTION** – Tested to the prestigious European EN1143-1 Security standard. ECB.S Certified Grade III has a recommended Insurance rating of £35,000 cash or £350,000 valuables*.
- **APPROVALS** – UK Police approved (Secured by Design scheme) and the Association of Insurance Surveyors (AiS).
- **FIRE PROTECTION** – Tested to the European LFS 30P fire protection standard (EN15659) giving 30 minutes fire protection for paper records.
- **KEY LOCKING** – Fitted with high security double bitted VdS class II key lock.
- **ELECTRONIC LOCKING** – Fitted with high security VdS class II electronic lock with dual control, master code & time delay.
- **FIXING** – Ready prepared for floor or wall fixing, with fixing bolts supplied for concrete floors or brick walls.
- **SPECIAL FEATURE** – Pre-prepared for alarm or power cable.
- **CONSTRUCTION** – 3 way angular locking bolts, double wall construction with specially formulated concrete infill and anti-drill plates, provide a safe of great strength.
- **COLOUR** – Finished in a high quality scratch resistant graphite grey paint RAL7024.
- **GDPR** – Maintain GDPR Compliance at home or in the office by keeping your company's vital and important records secure and protected.

+ Suitable for storage of controlled drugs whose active ingredients exceed 500 grams.

MODEL NUMBER	EXTERNAL DIMENSIONS H x W x D	INTERNAL DIMENSIONS H x W x D	DOOR SWING / HANDLE DEPTH	WEIGHT	CAPACITY	LEVER ARCH FOLDER	FOOLSCAP LEVER ARCH FOLDER	FOOLSCAP BOX FILE
						SHELVES (H320xW75x290mm) Total no. of file per unit	(H350xW80xD285mm) Total no. of file per unit	(H370xW75xD245mm) Total no. of file per unit
HS3551K/E	550 x 520 x 500mm	440 x 405 x 300mm	485mm/40mm	230/245kg	56 Litres	1	5	5
HS3552K/E	650 x 520 x 500mm	540 x 405 x 300mm	485mm/40mm	260/280kg	69 Litres	1	5	5
HS3553K/E	970 x 520 x 500mm	860 x 405 x 300mm	485mm/40mm	357/383kg	110 Litres	2	10	10
HS3554K/E	1280 x 650 x 500mm	1170 x 535 x 300mm	615mm/40mm	527/567kg	197 Litres	3	21	21
HS3555K/E	1630 x 860 x 500mm	1500 x 725 x 300mm	815mm/40mm	855/920kg	330 Litres	4	36	36

This information is provided as a guide only. Actual capacities may vary depending on the storage method or shelving used.



HS3550K

HS3550E

* Ratings are approximate only and may vary due to area conditions and location. Please check with your underwriter.