



TEMPERATURE MONITORING RELAY
THERMOCOUPLE TYP K, EXCEEDING 1 THRESH.
VAL., WIDTH 22ND5 MM 0 C - 200 C, 24V AC/DC 1 NO
+ 1 NC, CLOSED-CIRC.PRINC. SCREW
CONNECTION

Figure similar

General technical data:




Type of voltage		AC/DC
Supply voltage frequency		
<ul style="list-style-type: none"> • 1 for auxiliary and control current circuit — Initial rated value — Final rated value 	Hz	50
	Hz	60
Control supply voltage 1 with AC at 50 Hz		
<ul style="list-style-type: none"> • Rated value 	V	24
Control supply voltage 1 with AC at 60 Hz		
<ul style="list-style-type: none"> • Rated value 	V	24
Control supply voltage 1 for DC		
<ul style="list-style-type: none"> • Rated value 	V	24
Product function		
<ul style="list-style-type: none"> • Fault storage • External reset 		No
		No
Number of measuring circuits		1
Number of NC contacts for auxiliary contacts		1
Number of NO contacts for auxiliary contacts		1
Number of CO contacts for auxiliary contacts		0
Measurable temperature		
<ul style="list-style-type: none"> • initial value • Full-scale value 	°C	0
	°C	200
Equipment marking acc. to DIN EN 61346-2		K
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		K

Ambient temperature during operation	°C	-25 ... +60
--------------------------------------	----	-------------

Mechanical data:

Type of electrical connection		screw-type terminals
<ul style="list-style-type: none"> • for auxiliary and control current circuit • Plug-in socket 		Yes
Design of the sensor connectable		type K (thermocouple)
Width	mm	22.5
Height	mm	102
Depth	mm	91

Certificates/ approvals:

General Product Approval	Test Certificates	other			
 CCC	 EAC	 UL	Special Test Certificate	Environmental Confirmations	Declaration of Conformity

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RS11011CD20>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<http://support.automation.siemens.com/WW/view/en/3RS11011CD20/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RS11011CD20&lang=en>



last modified:



09.03.2015