

ISOL. TERMINAL THERMOPLASTIC SCREW
 TERMINAL ON BOTH ENDS W/O TEST SOCKET,
 8MM, SZ 6




Figure similar

Model		
Type of longitudinal separation		sliding
Type of lateral separation		without
Design of terminal / Terminal levels internally linked		No
General technical data		
Insulation material		thermoplastic
Terminal contact spacing	mm	8
Protection class		
Combustibility class acc. to UL 94		V2
Main circuit		
Operating voltage / Rated value	V	500
Operating current / Rated value	A	41
Appearance		
Color		beige
Product details		
Product component		
<ul style="list-style-type: none"> • required / connection plate • Test socket 		No No
Number		
Number of terminal levels		1
Number of terminal points / per terminal level		2
Connections		

Connectable conductor cross-section / stranded		
• minimum	mm ²	1.5
• maximum	mm ²	6
Connectable conductor cross-section		
• solid		
— minimum	mm ²	6
— maximum	mm ²	6
• finely stranded		
— with core end processing / minimum	mm ²	6
— with core end processing / maximum	mm ²	6
— without core end processing / minimum	mm ²	6
— without core end processing / maximum	mm ²	6
Type of electrical connection		
• 1		screw-type terminal
• 2		screw-type terminal
Position / of the terminal		lateral

Mechanical Design		
Height / with lowest-profile installation	mm	33
Length	mm	83
Mounting type		DIN rail 35 mm
Material / of the insulating body		Thermoplast

Environmental conditions		
Ambient temperature		
• during operation / minimum	°C	-25
• during operation / maximum	°C	55

General Product Approval	Test Certificates	Shipping Approval
---------------------------------	--------------------------	--------------------------



[other](#)



Shipping Approval	other
--------------------------	--------------



[Environmental Confirmations](#)

[other](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8WA10111MH11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8WA10111MH11/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8WA10111MH11

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015