

Offset clamp, with adjustable support screw, complete



Application:

For clamping workpieces.

Execution:

- With support screw and clamping screw
- Made from heat-treated steel
- Painted



Art. no.	26222 010
Brand	AMF
Manufacturer Part Number	71274
For table grooves according to DIN 650	10 mm
Suitable screw DIN 787	M10 x 80 mm
Min./max. clamping range	22-46 mm
Groove width	11 mm
Span iron length	100 mm
Span iron width	30 mm
Thread dimension	M10
Thread length	39 mm
Thickness	15 mm
Distance	36 mm
Length	32 mm
Gross Weight	0.420 kg
Product Group	260

EAN

4020772071271

