

Pump set F430 PP-40/33 electrical

Completely ready for use with PP suction pipe, pressure hose and pump nozzle



Application:

For pumping acids and alkalis.

Version:

- Collector motor, 230 V, 50 Hz, 500 W, shockproof, noise-suppressed
- Motor with undervoltage trip and continuous speed adjustment
- Set comes complete with PP pump pipe set with FKM seal
- 2-m PVC hose DN 19
- With PP hose connection and nozzle
- PP drum screw coupling, conductive



Art. no.	56359 490
Model	F430 PP-40/33
Max. immersion depth	1000 mm
Max. delivery height	9.5 m
Feed quantity	165 l/min
Suitable for container	60-200 litres
Max. temperature resistance	50 °C

EAN-Code

4260387213134