

Standing system workstation

With lighting

CLIP-O-FLEX®

Application:

Suitable for assembly, logistics, measuring and production workstations. When outstanding productivity and ergonomics are needed. Full integration of the CLIP-O-FLEX® interface to optimise workflows through flexible workstation design. Easily expandable with CLIP-O-FLEX® trays, boxes, tool holders and other accessories.

Execution:

- Modern 10 mm HPL worktop
- CLIP-O-FLEX support rail on side and front
- 3x CLIP-O-FLEX multi-purpose supply station
- Multiple socket outlet with three safety sockets
- Dimmable LED lighting
- Equipment rail incl. tool hangers



Art. no.	50237 330
Brand	CLIP-O-FLEX
Manufacturer Part Number	8796602
Type	StandingAL
Worktop width	1470 mm
Working height	900 mm
Worktop thickness	10 mm
Worktop depth	695 mm
Height	2100 mm
With lighting	Yes
With rollers	No
Anodised	Yes
Load-carrying capacity	400 kg
Material	Aluminium
Material of worktop	Hard pressure laminate board
Width	1500 mm
ESD-capable	No
Colour temperature	4000 K
Made in	Austria
Life time of illuminant	100000 h
Operating voltage	230 V/AC
Luminous flux	3294 lm
Operating temperature	40 °C
Min. colour rendering index (CRI)	85
Light length	953 mm
Luminaire efficacy	86 lm/W
Current consumption	16 A
IP protection type, lamp	IP 20
Depth	800 mm
Adjustable in height	No
Included in delivery	Fully assembled workstation, on pallet, 2 m ready-wired supply line, safety plug, incl. upper structure
Gross Weight	174.000 kg
Product Group	586