

Blind rivet nut hand tool

GBM 10 model



Version:

- With M5 threaded mandrel and nosepiece

Advantage:

- Simple to adjust the stroke using the knurled nut with stroke scale for secure and complete placement of the blind rivet nut
- Rapid replacement of threaded mandrels without the need for tools

Delivery:

replacement thread mandrels and nozzles available deliverable from stock - please request

Art. no.	53195 300
Model	GBM 10
Length	260 mm
Suitable for max. rivet diameter (rivet material: aluminium)	6 mm
Suitable for max. rivet diameter (rivet material: stainless steel)	5 mm

EAN-Code

4007081200011

