


**SBCT1020 ... SBCT10100**
**Schottky Barrier Rectifier Diodes – Common Cathode**  
**Schottky-Barrier-Gleichrichterdioden – Gemeinsame Kathode**

Version 2010-03-31



Nominal Current

10 A

Repetitive peak reverse voltage  
Periodische Spitzensperrspannung

20...100 V

Plastic case  
Kunststoffgehäuse

TO-220AB

Weight approx.  
Gewicht ca.

2.2g

Plastic material has UL classification 94V-0  
Gehäusematerial UL94V-0 klassifiziertStandard packaging in tubes  
Standard Lieferform in Stangen
**Maximum ratings and Characteristics**
**Grenz- und Kennwerte**



Type Typ	Repetitive peak reverse voltage Periodische Spitzensperrspannung $V_{RRM}$ [V]	Surge peak reverse voltage Stoßspitzensperrspannung $V_{RSM}$ [V]	Forward Voltage Durchlass-Spannung $V_F$ [V] <sup>1)</sup> <sup>2)</sup>	$I_F = 5$ A	$I_F = 10$ A
SBCT1020	20	20	< 0.55	< 0.63	
SBCT1030	30	30	< 0.55	< 0.63	
SBCT1040	40	40	< 0.55	< 0.63	
SBCT1045	45	45	< 0.55	< 0.63	
SBCT1050	50	50	< 0.70	< 0.79	
SBCT1060	60	60	< 0.70	< 0.79	
SBCT1090	90	90	< 0.85	< 0.92	
SBCT10100	100	100	< 0.85	< 0.92	

Max. average forward rectified current, R-load  
Dauergrenzstrom in Einwegschaltung mit R-Last $T_C = 100^\circ\text{C}$        $I_{FAV}$       5 A<sup>1)</sup>  
 $I_{FAV}$       10 A<sup>2)</sup>Repetitive peak forward current  
Periodischer Spitzenstrom $f > 15$  Hz       $I_{FPM}$       20 A<sup>2)</sup>Peak forward surge current, 50/60 Hz half sine-wave  
Stoßstrom für eine 50/60 Hz Sinus-HalbwelleSBCT1020...       $T_A = 25^\circ\text{C}$        $I_{FSM}$       100/120 A<sup>2)</sup>  
SBCT1060Peak forward surge current, 50/60 Hz half sine-wave  
Stoßstrom für eine 50/60 Hz Sinus-HalbwelleSBCT1080...       $T_A = 25^\circ\text{C}$        $I_{FSM}$       100/120 A<sup>2)</sup>  
SBCT10100Rating for fusing,  $t < 10$  ms  
Grenzlastintegral,  $t < 10$  ms $T_A = 25^\circ\text{C}$        $i^2t$       50 A<sup>2</sup>s 2)Junction temperature – Sperrschiesschichttemperatur  
Storage temperature – Lagerungstemperatur $T_j$       -50...+150°C  
 $T_s$       -50...+175°C1  $T_j = 25^\circ\text{C}$ 

1 Per diode – Pro Diode

**Characteristics**

			<b>Kennwerte</b>
Leakage current Sperrstrom	$T_j = 25^\circ\text{C}$ $T_j = 100^\circ\text{C}$	$V_R = V_{\text{RRM}}$	$I_R < 300 \mu\text{A}$ $< 7 \text{ mA}$
Thermal resistance junction to case Wärmewiderstand Sperrsicht - Gehäuse		$R_{\text{thC}}$	$< 3.0 \text{ K/W}^1)$



2 Per device (parallel operation) – Pro Bauteil (Parallelbetrieb)  
1 Per device (parallel operation) – Pro Bauteil (Parallelbetrieb)