

INSIDER internal deburring machine

Fits in all pillar drills with a chuck capacity of 10 mm

Application:

For internal deburring of cross holes in pipes, cylinders, steel sections, splines and other hard-to-reach bores.

Execution:


- Chatter mark-free countersinking in steel, non-ferrous or light metal as well as plastic and wood
- LH cutting countersinks (standard models) are installed pointing upwards, RH cutting countersinks pointing downwards
- Replaceable arm with lengths of 100/150/200 mm

Advantage:

- Maintenance free, long service life due to ball bearings
- Overload protection protects the toothed belts and tool

Delivery:

Appliance with telescopic dolly, arm either for 100 mm, 150 mm or 200 mm radius, 1 matching toothed belt, 2 hexagonal spanners 2 and 3 mm, 1 HSS LH countersink 90° each for diameters 7.0 mm, 10.4 mm and 19.0 mm (for internal diameter from 21 mm, 22 mm and 25 mm)



Art. no.	78260 015
Manufacturer Article Number	300111207
Model	83-150
Overhang	150 mm
Gross Weight	1.100 kg
Product Group	783