

# Temperature Sensor

## FXDD103

Part Number

weFlux<sup>2</sup> InoxSens



- FDA compliant
- Response time T90: < 2 seconds
- Robust stainless steel housing with IP69K
- Temperature measuring range: -50 ... +200° C


### Technical Data

| Sensor-specific data            |                      |
|---------------------------------|----------------------|
| Sensor element                  | PT1000, Class B      |
| Temperature Measurement Range   | -50...200 °C         |
| Medium                          | Liquids, gases       |
| Response Time                   | < 2 s                |
| Environmental conditions        |                      |
| Temperature of medium           | -50...200 °C         |
| Ambient temperature             | -25...80 °C          |
| Storage temperature             | -25...80 °C          |
| Pressure Resistance             | 100 bar              |
| Shock Resistance                | IEC 60751            |
| Vibration resistance            | IEC 60751            |
| Mechanical Data                 |                      |
| Housing Material                | 1.4404               |
| Material in contact with media  | 1.4404               |
| Degree of Protection            | IP68/IP69K *         |
| Connection                      | M12 × 1; 4-pin       |
| Process Connection              | Cutting/locking ring |
| Process Connection Length (PCL) | 209 mm               |
| Probe Length (PL)               | 200 mm               |
| Safety-relevant Data            |                      |
| MTTFd (EN ISO 13849-1)          | 31062,7 a            |

|                                   |           |
|-----------------------------------|-----------|
| PT1000                            | ●         |
| Connection Diagram No.            | 140       |
| Suitable Connection Equipment No. | 2         |
| Suitable Mounting Technology No.  | 907   908 |


\* Tested by wenglor

weFlux<sup>2</sup> Temperature Sensors ensure precise temperature measurement of liquids and gases in closed piping systems. It's easy to incorporate the standardized PT100/PT1000 resistance value into the controller. The compact housing with a diameter of just 27 mm is made of V4A stainless steel and features an easy-to-clean surface. Thanks to their rugged housing and functional design, the Temperature Sensors are FDA compliant.




### Complementary Products


ZH6C00x Adapter to G1/4"



All dimensions in mm (1 mm = 0.03937 Inch)



### Legend

|  |  |  |
|--|--|--|
| <b>+</b> Supply Voltage +  | <b>PT</b> Platinum measuring resistor              | <b>EN<sub>A/RS422</sub></b> Encoder A/ $\bar{A}$ (TTL) |
| <b>-</b> Supply Voltage 0 V  | <b>nc</b> not connected                            | <b>EN<sub>B/RS422</sub></b> Encoder B/ $\bar{B}$ (TTL) |
| <b>~</b> Supply Voltage (AC Voltage)   | <b>U</b> Test Input                                | <b>EN<sub>A</sub></b> Encoder A                        |
| <b>A</b> Switching Output (NO)   | <b>U</b> Test Input inverted                       | <b>EN<sub>B</sub></b> Encoder B                        |
| <b><math>\bar{A}</math></b> Switching Output (NC)  | <b>W</b> Trigger Input                             | <b>A<sub>MIN</sub></b> Digital output MIN              |
| <b>V</b> Contamination/Error Output (NO)   | <b>W-</b> Ground for the Trigger Input             | <b>A<sub>MAX</sub></b> Digital output MAX              |
| <b><math>\bar{V}</math></b> Contamination/Error Output (NC)  | <b>O</b> Analog Output                             | <b>A<sub>OK</sub></b> Digital output OK                |
| <b>E</b> Input (analog or digital)   | <b>O-</b> Ground for the Analog Output             | <b>SY<sub>in</sub></b> Synchronization In              |
| <b>T</b> Teach Input   | <b>BZ</b> Block Discharge                          | <b>SY<sub>OUT</sub></b> Synchronization OUT            |
| <b>Z</b> Time Delay (activation)   | <b>AWV</b> Valve Output                            | <b>OL<sub>T</sub></b> Brightness output                |
| <b>S</b> Shielding   | <b>a</b> Valve Control Output +                    | <b>M</b> Maintenance                                   |
| <b>RxD</b> Interface Receive Path  | <b>b</b> Valve Control Output 0 V                  | <b>rsv</b> reserved                                    |
| <b>TxD</b> Interface Send Path   | <b>SY</b> Synchronization                          | Wire Colors according to IEC 60757                     |
| <b>RDY</b> Ready   | <b>SY-</b> Ground for the Synchronization          | <b>BK</b> Black  |
| <b>GND</b> Ground  | <b>E+</b> Receiver-Line                            | <b>BN</b> Brown  |
| <b>CL</b> Clock  | <b>S+</b> Emitter-Line                             | <b>RD</b> Red  |
| <b>E/A</b> Output/Input programmable   | <b><math>\pm</math></b> Grounding                  | <b>OG</b> Orange                                       |
|  <b>IO-Link</b> | <b>S<sub>n</sub>R</b> Switching Distance Reduction | <b>YE</b> Yellow                                       |
| <b>PoE</b> Power over Ethernet   | <b>Rx+/-</b> Ethernet Receive Path                 | <b>GN</b> Green  |
| <b>IN</b> Safety Input   | <b>Tx+/-</b> Ethernet Send Path                    | <b>BU</b> Blue   |
| <b>OSSD</b> Safety Output  | <b>Bus</b> Interfaces-Bus A(+)/B(-)                | <b>VT</b> Violet                                       |
| <b>Signal</b> Signal Output  | <b>L<sub>a</sub></b> Emitted Light disengageable   | <b>GY</b> Grey   |
| <b>Bl..D+/-</b> Ethernet Gigabit bidirect. data line (A-D)   | <b>Mag</b> Magnet activation                       | <b>WH</b> White  |
| <b>EN<sub>0/RS422</sub></b> Encoder 0-pulse 0-0 (TTL)  | <b>RES</b> Input confirmation                      | <b>PK</b> Pink   |
|  | <b>EDM</b> Contactor Monitoring                    | <b>GNYE</b> Green/Yellow                               |

