


Capacitor, film, 0.15 uF, +/-10% Tol, -40/+110C, General Purpose, 630 VDC@105C, Lead Spacing=15 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	18	+0.3
H	12	+0.1
T	6	+0.2
S	15	+/-0.4
LL	30	+5/-0
F	0.6	+/-0.05

**Notes:**

-L,H,T are nominal dimensions and do not imply a minimum.

#### General Information

Supplier:	KEMET
Dielectric:	Metallized Polypropylene
Application:	General Purpose
Sub Application:	Pulse
Style:	Radial Box
Lead Form:	Wire Leads
RoHS:	Yes

#### Specifications

Capacitance:	0.15 uF
Voltage:	630 VDC
Tolerance:	+/-10%
Voltage AC:	275 VAC
Rated Temperature:	105C
Temperature Range:	-40/+110C
Dissipation Factor @ 1 kHz:	0.1%
Dissipation Factor @ 10 kHz:	0.1%
Dissipation Factor @ 100kHz:	0.1%
Insulation Resistance:	100 GOhm
Inductance:	10
Maximum dVdT:	250 v/us
Miscellaneous:	Above 105C DC and AC voltage derating is 4%/C

#### Packaging Specifications

Package Kind:	Bulk
Package Quantity:	900