

Electronic dial gauge

MarCator 1086 R-HR



Application:

For static measurements of lengths and length differences

Execution:

- Factor adjustable
- Large LCD display (11 mm)
- mm/inch changeover
- LOCK function (key lock)
- Permissible deviation MPEp 0.5 μ m

Advantage:

- High-resolution measuring system with digit increment 0.1 μ m

Delivery:

In case with CR 2450 battery



Art. no.	33166 614
Brand	MAHR
Manufacturer Part Number	4337698
Length measuring range	25 mm
Digit increment	0.0001 mm
Min./max. measurement force	0.65-1.15 N
Error limit	2.2 μ m
Repeat accuracy	0.5 μ m
Data transmission type	multiCOM
IP protection class	IP 42
Absolute function	Yes
Automatic switch-off	Yes
Preset function	Yes
Tolerance value entry	Yes
Number of rechargeable batteries/batteries	1 PCS
Rechargeable battery/battery capacity	540 mAh
Battery voltage	3 V
Weight of rechargeable battery/battery	0.0059 kg
Battery designation	3V CR2450N lithium
Rotating housing	Yes
Reversible counting direction	Yes
Calibration Group Description	Dial gauge
Calibration Group	CE
Gross Weight	0.300 kg
Product Group	305

EAN

4059192061685