


Load arm with fixed length

Horizontal incline

Application:

Extends the range of the forklift truck.

Art. no.	50262 259
Min./max. load-carrying capacity	250-2500 kg
Design	Fixed length
Boom tilt	Horizontal
Length	2400 mm
Width	600 mm
Fork, internal distance	160 mm
Internal width	220 mm
Interior height	80 mm
Colour	Light blue RAL 5012
Surface	Lacquered
Gross Weight	88.000 kg
Product Group	5AI



EAN

4052462039179