

**TEGERA® 8807
INFINITY**

Cut resistant glove, nitrile foam/waterbased PU, palm-dipped, CRF® Technology, glass fibre thread, nylon, spandex, 15 gg, foam grip pattern, cut resistance level 5, cut resistance level D, Cat. II, black, yellow, withstands contact heat up to 100°C, anatomically designed, for assembly work

PROPERTIES

High level of protection, good fingertip sensitivity, flexible, durable, good grip in oily environments, extra comfortable

SPECIFICATION

TYPE OF GLOVE Cut resistant gloves

CATEGORY Cat. II

CUT RESISTANCE (COUP) Cut resistance level 5

CUT RESISTANCE (EN ISO 13997) Cut resistance level D

CUT RESISTANCE (EN ISO 13997) NEWTON VALUE 17

SIZE RANGE (EU) 5, 6, 7, 8, 9, 10, 11

COLLECTION Infinity

LINER MATERIAL CRF® Technology, glass fibre thread, nylon, spandex, 15 gg

DIPPING Palm-dipped

DIPPING MATERIAL Nitrile foam/waterbased PU

DEXTERITY 5

GRIP PATTERN Foam grip pattern

CUFF STYLE Knitwrist cuff

COLOUR Black, yellow

PAIRS PER PACKAGE/CARTON 6/120

DISPLAY Hook

MATERIAL SPECIFICATION Nitrile, glass fibre thread, HPPE, nylon, elastane



I N F I N I T Y™



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

TEGERA® 8807 INFINITY

FEATURES

Cut resistant according to 388:2016 level D, withstands contact heat up to 100°C, approved for handling foodstuffs, water and oil repellent palm, anatomically designed

PREVENTS RISK OF

Cut injuries, abrasion injuries, blisters, grazes, scratches, lacerations, contact with dirt, drying out, chapping

PRIMARY ENVIRONMENTS OF USE

Dry environments, moist environments, dirty environments

PRIMARY AREAS OF USE

Fine assembly, assembly, machine operating, building and construction, carpentry, installation work, HVAC installation, sheet-metal work, engineering, transport work, machine driving, warehouse work, airport work, metalwork, glass industry work, repair work, paper industry work, service work, shop work

PRIMARY INDUSTRIES OF USE


Pulp and paper, glass, bricks, concrete, metal fabrication, machinery and equipment, MRO, automotive, transportation, utilities, building and construction, logistics, facilities, service, retail

TYPE OF WORK

Medium weight



CE Cat. II



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-05-14

2(4)

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com

TEGERA® 8807 INFINITY

EC TYPE EXAMINATION

Notified Body: 0075 CTC, 4 rue Hermann Frenkel, 69367 Lyon Cedex 07 France

COMPLIANCE DESCRIPTION

EN 420:2003 + A1:2009 Protective gloves - general requirements and test methods

EN 388:2016 Protective gloves against mechanical risks

Property	Level Achieved	(Maximum Performance)
a) Resistance to abrasion (No. of revolutions)	4	(4)
b) Cut resistance (Index)	X	(5)
c) Tear resistance (N)	4	(4)
d) Puncturing resistance (N)	3	(4)
e) Cut resistance, EN ISO 13997 (N)	D	(F)
f) Impact protection, EN 13594:2015		(P)

EN 388 - Testing

(specifies the requirements that apply for each safety level).


Level of protection/Performance level	1	2	3	4	5
a) Resistance to abrasion (No. of revolutions)	100	500	2000	8000	
b) Cut resistance (Index)	1,2	2,5	5,0	10,0	20,0
c) Tear resistance (N)	10	25	50	75	
d) Puncturing resistance (N)	20	60	100	150	

Level of protection/Performance level	A	B	C	D	E	F
e) Cut resistance, EN ISO 13997 (N)	2	5	10	15	22	30

Level of protection/Performance level	P
f) Impact protection, EN 13594:2015	Pass (Level 1 ≤ 9 kN)



CE Cat. II



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-05-14

3(4)

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com


TEGERA® 8807 INFINITY


EN 407:2004 Protective gloves against thermal risks (heat and/or fire)

CONFIDENCE IN TEXTILES Tested for harmful substances according to Oeko-Tex® Standard 100



CE Cat. II

 EN 388:2016
4X43D

 EN 407:2004
X1XXXX



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-05-14

4(4)

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com