

## SDUC boring bar, offset, HSS positive, left-hand

For longitudinal and copy turning with DC indexable insert

**ATORN**<sup>®</sup>

### Application


For longitudinal and copy turning with DC indexable insert 55°.

### Version

- Precision-made boring bar, **HSS**, with internal cooling, offset, type D, attack angle 93.5°, tip angle 55°, clearance angle 7°

### Advantage

- Narrow contour optimised for copying-turning work
- Positive body geometry ensures low cutting forces
- Very high rigidity and very good cut quality due to HSS base material



<b>Art. No.</b>	<b>17847 219</b>
<b>ISO name</b>	AH 1012 K SDUC R/L 07
<b>Min. bore diameter</b>	15.5 mm
<b>Shaft diameter</b>	12 mm
<b>Clearance length</b>	28 mm
<b>Length</b>	125 mm
<b>Clamping surface height</b>	11 mm
<b>Programming size</b>	9 mm
<b>Suitable for indexable inserts</b>	DC.. 0702..
<b>Tool design</b>	Left
<b>DIN</b>	8024

### EAN-Code

4050293111088