

Male headers soldering technique

□ 0,635 mm, Sandwich

<b>art. no.</b>	dim. [mm]		<b>art. no.</b>	dim. [mm]	
	A	L		A	L
<b>SL 13 071 ...</b>	7.10	21.40	<b>SL 13 235 ...</b>	23.50	37.80
<b>SL 13 097 ...</b>	9.70	24.00	<b>SL 13 265 ...</b>	26.50	40.80
<b>SL 13 122 ...</b>	12.20	26.50	<b>SL 13 310 ...</b>	31.00	45.30
<b>SL 13 147 ...</b>	14.70	29.00	<b>SL 13 365 ...</b>	36.50	50.80
<b>SL 13 187 ...</b>	18.70	33.00			
<b>art. no.</b>	dim. [mm]		<b>art. no.</b>	dim. [mm]	
	A	L		A	L
<b>SL 14 071 ...</b>	7.10	21.40	<b>SL 14 235 ...</b>	23.50	37.80
<b>SL 14 097 ...</b>	9.70	24.00	<b>SL 14 265 ...</b>	26.50	40.80
<b>SL 14 122 ...</b>	12.20	26.50	<b>SL 14 310 ...</b>	31.00	45.30
<b>SL 14 147 ...</b>	14.70	29.00	<b>SL 14 365 ...</b>	36.50	50.80
<b>SL 14 187 ...</b>	18.70	33.00			
<b>please indicate:</b>	... no. of contacts one row 1-36 two rows 2-72		... surface S = selective gold-plated G = gold-plated Z = tin-plated		

"S" selective gold-plated to 33.0 mm pin length

For interconnections of stacked PCBs. The male headers SL 13 and SL 14 are used to connect BL 11 (SL 13 ...) and BL 12 (SL 14 ...). Suitable for PCBs 1.5 mm - 3.0 mm thick.

V-notches permit breaking! Therefore any required number of contacts is available. Every pin length is available on request.

- |                                     |             |                                    |             |
|-------------------------------------|-------------|------------------------------------|-------------|
| Female headers 2.54 solder          | → G 27      | Jumpers                            | → G 72 - 73 |
| Fem. head. 2.54 solder, put through | → G 28      | Special male & female headers      | → G 19      |
| Female headers 2.54 SMD             | → G 41 - 44 | High-prec. fem. headers 2.54 sold. | → G 30 - 33 |
| IDC-connectors                      | → H 1 - 14  | Technical data                     | → G 72 - 76 |