

Swarf containers, tip from the forklift operator's seat

Carrying capacity up to 1500 kg, perforated metal plate over entire floor

Application:

For the collection and separation of liquids from solids and for the transport or disposal of all types of waste, bulk materials, chips and mass-produced parts.

Version:

- Perforated metal plate screwed across the entire base, 100 mm above the base, hole diameter 3 mm, spacing 6 mm
- Drain valve 1" for draining off liquids
- Tilting at any height using a wire rope from the stacker seat
- Sheet metal tray with surrounding edge profile
- Sturdy base frame with fork pockets
- Protection against accidental slipping and tipping

Delivery:

Goods supplied without packaging as standard. Packaging available for an additional charge.



Art. no.	50266 350
Volume	0.3 m ³
Length	1440 mm
Width	680 mm
Tipper edge height	395 mm
Height	580 mm
Fork pocket clearance	10 mm
Fork pocket size (W x H)	200 x 60 mm
With drain valve	Yes
With stacker seat tilt function	Yes
With perforated sheet	Yes
Load-carrying capacity	750 kg
Surface	Lacquered
Colour	Optional