

Multi-functional table trolley

With steel cabinet, load capacity 125 kg

LUXOR
PROVIDING KNOWLEDGE PROJECT SOLUTIONS

Application:

This popular all-purpose trolley safely stores and transports your valuable electronic devices from room to room.

Execution:

- The steel construction and the robot-welded trays guarantee a long service life even in harsh environments
- Textured mats and an all-round stop edge keep the contents of the trays securely in place
- This height-adjustable multi-functional trolley is easy to manoeuvre thanks to the four fully swivelling castors
- Can be quickly stabilised if necessary with the two installed locking brakes
- The height is adjustable in increments of 50 mm
- Height adjustment range: 610-1070 mm
- The integrated steel cabinet is lockable (incl. 2 keys) and has a recessed handle

Advantage:

- Height-adjustable
- Agile
- Durable
- Low-noise, ball-bearing swivel castors

Delivery:

Supplied disassembled - easy assembly



Art. no.	50311 032
Brand	LUXOR
Manufacturer Part Number	SEAVJ42C-RB
Load-carrying capacity	125 kg
Number of loading surfaces	2
Load-carrying capacity of loading surfaces	45 kg
Length	610 mm
Length x width x height	610 x 460 x 1070 mm
Width	460 mm
Height	1070 mm
Surface	Powder-coated
Wheel diameter	100 mm
Material of wheel	PP - Polypropylene
Number of steering rollers	4
With wheel lock	Yes
Colour	Blue
Made in	USA
Adjustable in height	Yes
Min. height adjustment	610 mm
Max. height adjustment	1070 mm
Min./max. height adjustment	610-1070mm
Gross Weight	28.000 kg
Product Group	5AQ

EAN

4260563729558