

## Pneumatic straight grinder SRH 8-10

With lever valve



### Application:

For lighter work with brushes and flap wheels.

### Execution:

- Rear air exhaust
- Double layering

### Advantage:

- Small, light and strong with reduced speed.

### Delivery:

Includes collet chuck ZG 7/6 mm and collet chuck key size 11 + 14; in box



|   |                     |
|---|---------------------|
| <b>Art. no.</b>                                 | <b>75036 080</b>    |
| <b>Brand</b>                                    | BIAX DRUCKLUFT      |
| <b>Manufacturer Part Number</b>                 | 150010980           |
| <b>Model</b>                                    | SRH 8-10            |
| <b>Valve design</b>                             | Lever valve         |
| <b>Motor design</b>                             | Vane motor          |
| <b>Max. idle speed</b>                          | 10000 rpm           |
| <b>Power output</b>                             | 280 W               |
| <b>Air consumption</b>                          | 300 l/min           |
| <b>Length</b>                                   | 218 mm              |
| <b>Diameter of housing</b>                      | 38 mm               |
| <b>Max. clamping diameter</b>                   | 8 mm                |
| <b>Collet chuck diameter</b>                    | 6 mm                |
| <b>Max. HM rotating milling cutter diameter</b> | 16 mm               |
| <b>Weight</b>                                   | 0.645 kg            |
| <b>Made in</b>                                  | Germany             |
| <b>Compatible with</b>                          | Hose unit 001366505 |
| <b>Gross Weight</b>                             | 1.200 kg            |
| <b>Product Group</b>                            | 748                 |