



## Residual current circuit breaker (RCCB), 40A, 4p, 30mA, type G/F

**Part no.** PFIM-40/4/003-G/F  
**Article no.** 187456



Similar to illustration

### Delivery programme

|                              |                |    |   |
|------------------------------|----------------|----|---|
| Basic function               |                |    | Residual current circuit breakers                                       |
| Number of poles              |                |    | 4 pole  |
| Application                  |                |    | Switchgear for residential and commercial applications                  |
| Rated current                | $I_n$          | A  | 40  |
| Rated short-circuit strength | $I_{cn}$       | kA | 10 with back-up fuse  |
| Rated fault current          | $I_{\Delta N}$ | A  | 0.03  |
| Type                         |                |    | Typ G/F (ÖVE E 8601)  |
| Tripping                     |                | A  | Short time-delayed  |
| Product range                |                |    | PFIM-F  |
| Sensitivity                  |                |    | pulse-current sensitive - frequency composition (10 Hz, 50 Hz, 1000 Hz) |
| Impulse withstand current    |                |    | Surge-proof, 3 kA   |

### Technical data

#### Electrical

|  |                      |            |   |
|--|----------------------|------------|---|
| Types conform to   |                      |            | IEC/EN 62423  |
| Current test marks   |                      |            | As per inscription  |
| Rated operating voltage  | $U_n$                | V AC       | 230/400   |
| Rated frequency  | f                    | Hz         | 50  |
| Limit values of the operating voltage  |                      |            |   |
| Test circuit   |                      | V AC       | 196 - 264   |
| Rated frequency  | f                    | Hz         | 50  |
| Sensitivity  |                      |            | pulse-current sensitive - frequency composition (10 Hz, 50 Hz, 1000 Hz)                   |
| Rated insulation voltage   | $U_i$                | V          | 440   |
| Rated impulse withstand voltage  | $U_{imp}$            | kV         | 4 (1.2/50 $\mu$ s)  |
| Rated short-circuit strength   | $I_{cn}$             | kA         | 10 with back-up fuse  |
| Max. admissible back-up fuse   |                      |            |   |
| Short-circuit  | gG/gL                | A          | 63  |
| Overload   | gG/gL                | A          | 25  |
| Rated making and breaking capacity / Rated residual making and breaking capacity | $I_m / I_{\Delta m}$ | A          | 500   |
| lifespan   |                      |            |   |
| Electrical   |                      | Operations |  2000  |
| Mechanical   |                      | Operations |  10000 |

#### Mechanical

|                          |  |                 |   |
|--------------------------|--|-----------------|---|
| Standard front dimension |  | mm              | 45  |
| Device height            |  | mm              | 80  |
| Built-in width           |  | mm              | 35 (2TE)  |
| Mounting                 |  |                 | Quick attachment with 2 latch positions for DIN-rail IEC/EN 60715         |
| Degree of Protection     |  |                 | IP20 switches<br>IP 40 enclosed   |
| Terminals top and bottom |  |                 | Twin-purpose terminals  |
| Terminal protection      |  |                 | Busbar tag shroud to BGV A3, ÖVE-EN 6                                     |
| Terminal cross-section   |  |                 |   |
| Solid                    |  | mm <sup>2</sup> | 1.5 - 35  |
| Stranded                 |  | mm <sup>2</sup> | 2 x 16  |
| Terminal cross-section   |  |                 | M5 (with cross-recessed screw as defined in EN ISO 4757-Z2, Pozidriv PZ2) |

|  |  |     |                           |
|--|--|-----|---------------------------|
| Tightening torque of fixing screws             |  | N/m | 2 - 2.4                   |
| Thickness of busbar material                   |  | mm  | 0.8 - 2                   |
| Admissible ambient temperature range           |  | °C  | -25 - +40                 |
| Permissible storage and transport temperatures |  | °C  | -35 - +60                 |
| Climatic proofing                              |  |     | according to IEC/EN 61008 |
| Mounting position                              |  |     | As required               |
| Contact position indicator                     |  |     | red / green               |

## Design verification as per IEC/EN 61439

| Technical data for design verification   |           |   |      |
|--|-----------|---|------|
| Rated operational current for specified heat dissipation   | $I_n$     | A | 40   |
| Equipment heat dissipation, current-dependent  | $P_{vid}$ | W | 13.1 |
| IEC/EN 61439 design verification   |           |   |      |
| 10.2 Strength of materials and parts   |           |   |      |
| 10.2.2 Corrosion resistance  |           |   |      |
| Meets the product standard's requirements.   |           |   |      |
| 10.2.3.1 Verification of thermal stability of enclosures   |           |   |      |
| Meets the product standard's requirements.   |           |   |      |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat   |           |   |      |
| Meets the product standard's requirements.   |           |   |      |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects           |           |   |      |
| Meets the product standard's requirements.   |           |   |      |
| 10.2.4 Resistance to ultra-violet (UV) radiation   |           |   |      |
| Meets the product standard's requirements.   |           |   |      |
| 10.2.5 Lifting   |           |   |      |
| Does not apply, since the entire switchgear needs to be evaluated.   |           |   |      |
| 10.2.6 Mechanical impact   |           |   |      |
| Does not apply, since the entire switchgear needs to be evaluated.   |           |   |      |
| 10.2.7 Inscriptions  |           |   |      |
| Meets the product standard's requirements.   |           |   |      |
| 10.3 Degree of protection of ASSEMBLIES  |           |   |      |
| Does not apply, since the entire switchgear needs to be evaluated.   |           |   |      |
| 10.4 Clearances and creepage distances   |           |   |      |
| Meets the product standard's requirements.   |           |   |      |
| 10.5 Protection against electric shock   |           |   |      |
| Does not apply, since the entire switchgear needs to be evaluated.   |           |   |      |
| 10.6 Incorporation of switching devices and components   |           |   |      |
| Does not apply, since the entire switchgear needs to be evaluated.   |           |   |      |
| 10.7 Internal electrical circuits and connections  |           |   |      |
| Is the panel builder's responsibility.   |           |   |      |
| 10.8 Connections for external conductors   |           |   |      |
| Is the panel builder's responsibility.   |           |   |      |
| 10.9 Insulation properties   |           |   |      |
| 10.9.2 Power-frequency electric strength   |           |   |      |
| Is the panel builder's responsibility.   |           |   |      |
| 10.9.3 Impulse withstand voltage   |           |   |      |
| Is the panel builder's responsibility.   |           |   |      |
| 10.9.4 Testing of enclosures made of insulating material   |           |   |      |
| Is the panel builder's responsibility.   |           |   |      |
| 10.10 Temperature rise   |           |   |      |
| The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |           |   |      |
| 10.11 Short-circuit rating   |           |   |      |
| Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |           |   |      |
| 10.12 Electromagnetic compatibility  |           |   |      |
| Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |           |   |      |
| 10.13 Mechanical function  |           |   |      |
| The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |           |   |      |

## Technical data ETIM 6.0

| Circuit breakers and fuses (EG000020) / Residual current circuit breaker (RCCB) (EC000003)   |  |    |          |
|--|--|----|----------|
| Electric engineering, automation, process control engineering / Electrical installation, device / Residual current protection system / Residual current circuit breaker (RCCB) (ecl@ss8.1-27-14-22-01 [AAB906011]) |  |    |          |
| Number of poles  |  |    | 4        |
| Nominal rated voltage  |  | V  | 230      |
| Nominal rated current  |  | A  | 40       |
| Rated fault current  |  | A  | 0.03     |
| Mounting method  |  |    | DIN rail |
| Leakage current type   |  |    | -        |
| Selective protection   |  |    | No       |
| Short-circuit breaking capacity (I <sub>cw</sub> )   |  | kA | 10       |
| Surge current capacity   |  | kA | 3        |
| Frequency  |  |    | 50 Hz    |
| Additional equipment possible  |  |    | Yes      |

|  |  |    |      |
|--|--|----|------|
| Degree of protection (IP)                        |  |    | IP20 |
| Construction size (in accordance with DIN 43880) |  |    | 1    |
| Width in number of modular spacings              |  |    | 4    |
| Built-in depth                                   |  | mm | 70.5 |
| Short-time delayed tripping                      |  |    | Yes  |