

**MIRO 6.2 OPTO-COUPLER MODULE**


IN: 230 VAC/DC - OUT: 253 VAC/DC / 0,5 A

Multi voltage output


Transistor 0.5 A

24...230 V AC/DC

Spring clamp terminals

[Link to Product](#)**Illustration**

stay connected



Product may differ from Image

### Input

|                   |                  |
|-------------------|------------------|
| Voltage range ON  | 10...230 V AC/DC |
| Voltage range OFF | 0...5 V AC/DC    |
| Control current   | 5 mA             |
| LED display       | LED (yellow)     |

### General data

|                        |                                |
|------------------------|--------------------------------|
| Test isolation voltage | 2.75 kV                        |
| Dimensions H × W × D   | 78×6.5×65                      |
| Mounting method        | DIN-rail mountable (EN 60715)  |
| Housing                | Black plastic, flame retardant |
| Temperature range      | -20...+60 °C                   |

### Output

|                                    |                  |
|------------------------------------|------------------|
| Switching time ON/OFF              | 5/15 ms          |
| Switching voltage                  | 10...230 V AC/DC |
| Switching current per output       | 1 mA...0.5 A     |
| Saturation voltage (across output) | max. 2.6 V AC/DC |
| Leakage current (output is open)   | max. 20 µA       |
| Switching frequency                | max. 2.5 Hz      |

### Commercial data

|                        |          |
|------------------------|----------|
| country of origin      | CZ       |
| customs tariff number  | 85414090 |
| minimum order quantity | 1        |