



LED COVER FOR POSITION SWITCH PLASTIC
3SE52, FOR HOUSING ACC. TO EN50047,31MM
LEDS 24V DC YELLOW/GREEN YELLOW

Product designation	cover for enclosures EN 50047, plastic, yellow, LEDs 24 V DC
---------------------	---

General technical data:

Shock resistance	30g / 11 ms
Vibration resistance	0.35 mm / 5g
Protection class IP	IP65
Explosion protection category for dust	none
Explosion protection category for gas	none

Enclosure:

Design of the housing	block, narrow
Coating of the enclosure	Other types

Drive Head:

Design of the operating mechanism	without
-----------------------------------	---------

Communication/ Protocol:

Design of the interface	without
-------------------------	---------

Ambient conditions:

Ambient temperature		
• during operation	°C	-25 ... +60
• during storage	°C	-40 ... +90

Supply voltage:

Type of voltage of the supply voltage		
• of the optional LED indicator		DC
Supply voltage		

• of LED

V

24

Installation/ mounting/ dimensions:

mounting position	any
Mounting type	screw fixing

Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates
 CCC		 EG-Konf.
 CSA		Special Test Certificate
 UL		

other

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SE52301AA001AG0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SE52301AA001AG0/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SE52301AA001AG0&lang=en



last modified:

16.03.2015