


RFSMAA4JCCBFGB Datasheet

Product Name // SMA Straight Jack 4 Hole Flange RF Connector

[View Product Page](#)



| // Product Description: | |
|---|---|
| <ul style="list-style-type: none"> ⊕ SMA Straight Jack 4 Hole Flange RF Connector ⊕ Maximum Voltage: 335V ⊕ Temperature range: -65Å°C to +165Å°C ⊕ Frequency range: 0GHz - 26.5GHz ⊕ VSWR: | <ul style="list-style-type: none"> ⊕ Dielectric withstanding Voltage: >750V ⊕ Impedance: 50Ohm ⊕ Body Material: Stainless Steel Passivation ⊕ Contact Material: Beryllium Copper |

| // General Information: | |
|----------------------------------|---|
| Product Display Title: | SMA Series Pin with Extended PTFE 4 Hole Flange |
| Product Family: | Radio Frequency Connectors |
| Product Series: | SMA Series |
| Body Length: | 9.30mm |
| Body Material: | Stainless Steel Passivation |
| Centre Contact Retention Force: | >26.7N |
| Contact Pin Material: | Beryllium Copper |
| Min Coupling Torque: | 0.80Nm |
| Max Coupling Torque: | 1.10Nm |
| Coupling Nut Retention Force: | >27.2Kg |
| Dielectric Withstanding Voltage: | >750V |
| Durability: | >500 cycles |
| Flange Mount Length: | 12.70mm |
| Function: | Female Flange Mount RF Connector |
| Impedance: | 50Ohm |
| Insulation Resistance: | >5000MOhm |
| Insulator: | Adapter ASTM D 1710 |
| Max Operating Temperature: | +165°C |
| Min Operating Temperature: | -65°C |
| Mount Hole Distance: | 8.60mm |
| Min Operating Frequency: | 0GHz |
| Max Operating Frequency: | 26.5GHz |
| Pin Diameter: | 0.38mm |
| Pin Length: | 2.00mm |
| Ptfe Diameter: | 4.00mm |
| Ptfe Length: | 3.00mm |
| Thread Size: | 1/4 36UNS 2A |
| Voltage Max: | 335V |
| Vswr: | <1.30 |

// Product PDF Links

[SMA Series Product Datasheet](#)