

SC torus milling cutter

4 cutters, ULTRA-coated

Application:

Torus milling cutter for universal machining.

Execution:

- Solid carbide ultra-fine grain
- Straight shank in accordance with DIN 6535 HB
- ULTRA-coated
- Centre cutting
- Twist angle 35°/38° with unequal cutting pitch
- Edge radius
- 2-fold twisted internal coolant supply to front cutters
- With clearance



Art. no.	16839 358
Cutting material	SC
Surface	ULTRA
Type	N
Number of cutting edges	4 PCS
Twist angle	35°, 38°
Tool holding device	HB parallel shank
Construction length	Normal
Cutting edge diameter	8 mm
Cutting edge length	19 mm
Clearance length	27 mm
Length	63 mm
Clearance diameter	7.6 mm
Shank diameter	8 mm
Edge radius	1 mm
fz steel 1000	0.05 mm
Gross Weight	0.010 kg
Product Group	148