



LV HRC FUSE LINK GL/GG WITH NON-INSULATED GRIP LUGS WITH FRONT INDICATOR SIZE 00, 63A, AC 690V/DC 250V

Figure similar

| Model                                 |  |                              |
|---------------------------------------|--|------------------------------|
| product brand name                    |  | SENTRON                      |
| Product designation                   |  | LV HRC fuse link             |
| Design of an identification indicator |  | Front indicators             |
| Design of the switching contact       |  | Non-corroding, silver-plated |
| Design of the fuse link               |  | LV HRC fuse link             |

| General technical data                       |  |                         |
|--|--|-------------------------|
| Size of fuse system / acc. to DIN EN 60269-1 |  | NH00                    |
| Operating class of the fuse link             |  | gG                      |
| circuit-breaker / Design                     |  | 3NA3                    |
| Mounting type                                |  | Non-insulated grip lugs |

| Protection class    |  |                                 |
|---------------------|--|---------------------------------|
| Protection class IP |  | IP20, with connected conductors |

| Switching capacity   |    |     |
|--|----|-----|
| <b>Switching capacity current</b>  |    |     |
| <ul style="list-style-type: none"> <li>for DC / acc. to IEC 60947-2 / Rated value</li> </ul> | kA | 25  |
| <ul style="list-style-type: none"> <li>acc. to IEC 60947-2 / Rated value</li> </ul>          | kA | 120 |

| Dissipation  |   |      |
|--|---|------|
| <b>Active power loss</b>   |   |      |
| <ul style="list-style-type: none"> <li>for rated value of the current / with AC / in hot operating state / per pole</li> </ul> | W | 5.42 |

| Electricity   |   |       |
|---|---|-------|
| rated current I <sub>n</sub> / IEC, DIN/VDE / at 40 Cel | A | 59.85 |

|                                 |   |    |
|---------------------------------|---|----|
| Current / with AC / Rated value | A | 63 |
|---------------------------------|---|----|

### Mechanical Design

|                   |                          |
|-------------------|--------------------------|
| mounting position | Any, preferably vertical |
|-------------------|--------------------------|

### Environmental conditions

|                            |    |                           |
|----------------------------|----|---------------------------|
| <b>Ambient temperature</b> |    |                           |
| • minimum                  | °C | -5                        |
| • maximum                  | °C | 40                        |
| • during storage / Note    |    | Air humidity 90% at 20 °C |

### Certificates



|                          |  |   |
|--------------------------|--|---|
| <b>Equipment marking</b> |  |   |
| • acc. to DIN EN 61346-2 |  | F |
| • acc. to DIN EN 81346-2 |  | F |

| General Product Approval  | Declaration of Conformity | Test Certificates                        |
|---|---------------------------|--|
|  CCC<br> GOST<br> VDE<br> EAC<br> EG-Konf. |                           | <a href="#">Special Test Certificate</a> |

| Test Certificates                                  | other   |
|--|---|
| <a href="#">Type Test Certificates/Test Report</a> | <a href="#">other</a><br><a href="#">Environmental Confirmations</a><br><a href="#">other</a> |

### Further information

- Information- and Downloadcenter (Catalogs, Brochures,...)**  
<http://www.siemens.com/lowvoltage/catalogs>
- Industry Mall (Online ordering system)**  
<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NA38226>
- Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**  
<http://support.automation.siemens.com/WW/view/en/3NA38226/all>
- Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**  
[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NA38226](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NA38226)
- CAX-Online-Generator**  
<http://www.siemens.com/cax>
- Tender specifications**  
<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015