



Figure similar

General technical data:

<b>Type of voltage</b>		DC
<b>Control supply voltage</b>		
<ul style="list-style-type: none"> <li>• for DC Rated value</li> </ul>		
— minimum	V	24
— maximum	V	24
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		3
<b>Operating current of the auxiliary contacts</b>		
<ul style="list-style-type: none"> <li>• at AC-15</li> </ul>		
— at 230 V	A	5
<b>Design of the switching function positively driven</b>		No
<b>Switching behavior</b>		monostable

Mechanical data:

<b>Type of electrical connection</b>		screw-type terminals
<b>Design of the relay operating mechanism</b>		poled
<b>Product component Plug-in socket</b>		No
<b>Width</b>	mm	35.5
<b>Height</b>	mm	36.5
<b>Depth</b>	mm	69

Certificates/ approvals:



[Declaration of  
Conformity](#)

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=LZX:MT321024>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/LZX:MT321024>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=LZX:MT321024&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=LZX:MT321024&lang=en)

last modified:

15.01.2015