



Section 1. Product and Company Identification.

1.1 Model Number; SCS400 v1
1.2 Description; Slow-Set 20 Min Epoxy Adhesive 25ml

1.3 Manufacturer;

Sealey Group.
Kempson Way,
Bury St. Edmunds,
Suffolk.
IP32 7AR

1.4 Emergency telephone number; 44 (0) 1284 757 500 (Office Hours)

Date of source compilation; 11 May 2012

Section 2. Hazards Identification.

2.1 Classification of the substance or mixture.

Acute Tox. 4: H302; Repr. 2: H361; Aquatic Acute 1: H400; Aquatic Chronic 1: H410;
Skin Corr. 1B: H314; Skin Sens. 1: H317

Risk phrases;

R21/22 Harmful in contact with skin and if swallowed.
R34 Causes burns.
R43 May cause sensitisation by skin contact.
R50/53 Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R62 Possible risk of impaired fertility.
R63 Possible risk of harm to the unborn child.

Safety phrases;

S1/2 Keep locked up and out of the reach of children.
S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S29 Do not empty into drains.
S36/37/39 Wear suitable protective clothing, gloves and eye / face protection.
S45 In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).
S61 Avoid release to the environment. Refer to special instructions / safety data sheets.

Most important adverse effects:

Harmful in contact with skin and if swallowed.
Causes burns.
May cause sensitisation by skin contact.
Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
Possible risk of impaired fertility.
Possible risk of harm to the unborn child.

Section 2. Hazards Identification, continued.

2.2 Label elements.

Hazard pictogram(s)



Signal Word. Danger

Hazard statements;

- H302 Harmful if swallowed.
- H314 Causes severe skin burns and eye damage.
- H317 May cause an allergic skin reaction.
- H361 Suspected of damaging fertility. Suspected of damaging the unborn child.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.

Precautionary statements;

- P102: Keep out of reach of children.
- P280: Wear protective gloves/protective clothing/eye protection/face protection.
- P301+310: IF SWALLOWED: Immediately call a POISON CENTER or doctor.
- P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- P308+313: IF exposed or concerned: Get medical advice/attention.

2.3 Other hazards.

No information available.

Section 3. Substances.

3.1 Chemical Name (substance)	3.1 CAS No.	3.2 Concentration Weight	Classification	
			Hazard Class & Category Code	Hazard Statements
Nonylphenol	25154-52-3	50 - 90%	Repr. 2 Acute Tox. 4 Skin Corr. 1B Aquatic Acute 1 Aquatic Chronic 1	H361 H302 H314 H400 H410
2-Piperazin-1-Ylethylamine	140-31-8	10 - 30%	Acute Tox. 4 Acute Tox. 4 Skin Corr. 1B Skin Sens. 1 Aquatic Chronic 3	H312 H302 H314 H317 H412

For full text of Phrases and Statements, see Section 16.



Section 4. First Aid Measures.

4.1 Description of first aid measures

Inhalation

Remove casualty from exposure ensuring one's own safety whilst doing so.

If unconscious and breathing is regular, place in the recovery position.

If conscious, ensure the casualty sits or lies down.

Get medical attention as soon as possible.

Skin Contact

Remove all contaminated clothes and footwear immediately unless stuck to skin.

Drench the affected skin with running water for 10 minutes or longer if substance is still on skin.

Get medical attention if there are burns or symptoms of poisoning.

Eye Contact

Bathe the eye with running water for 15 minutes.

Get medical attention.

Ingestion

Wash out mouth with water.

Do not induce vomiting.

Give 1 cup of water to drink every 10 minutes.

If unconscious, check for breathing and apply artificial respiration if necessary.

If unconscious and breathing is regular, place in the recovery position.

Get medical attention as soon as possible.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation: There may be shortness of breath with a burning sensation in the throat.
Exposure may cause coughing or wheezing.

Skin contact: Blistering may occur.
Progressive ulceration will occur if treatment is not immediate.

Eye contact: Corneal burns may occur.
May cause permanent damage.

Ingestion: Corrosive burns may appear around the lips.
Blood may be vomited.
There may be bleeding from the mouth or nose.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment:

Eye bathing equipment should be available on the premises.

A decontamination shower should be available on the premises.



Section 5. Fire Fighting Measures.

5.1. Extinguishing media

Carbon dioxide. Dry chemical powder. Alcohol resistant foam.

Do not use direct water stream, as this may spread the fire.

Water can be used to cool fire exposed containers

5.2. Special hazards arising from the substance or mixture

Corrosive. In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Wear self-contained breathing apparatus.

Wear protective clothing to prevent contact with skin and eyes.

Section 6. Accidental Release Measures.

6.1. Personal precautions, protective equipment and emergency procedures

If outside keep bystanders upwind and away from danger point.

Mark out the contaminated area with signs and prevent access to unauthorised personnel.

Do not attempt to take action without suitable protective clothing.

Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Do not discharge into drains or rivers.

Contain the spillage using bunding.

Discharge into watercourses must immediately be alerted to the Environment Agency or other appropriate regulatory body.

6.3. Methods and material for containment and cleaning up

Clean-up should be dealt with only by qualified personnel familiar with the specific substance.

Absorb into dry earth or sand.

Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

See Section 7 for information on Safe Handling

See Section 8 for information of Personal Protective Equipment.

See Section 13 for information on disposal.



Section 7. Handling and Storage.

7.1. Precautions for safe handling

Avoid direct contact with the substance.
Ensure there is sufficient ventilation of the area.
Do not handle in a confined space.
Avoid the formation or spread of mists in the air.

7.2. Conditions for safe storage, including any incompatibilities

Store in cool, well-ventilated area. Keep container tightly closed.
Must only be kept in original packaging.

7.3. Specific end use(s)

Intended for use as Slow-Set 20 Min Epoxy Adhesive: Model Number identified in 1.1 with Description stated in 1.2.

Section 8. Exposure Controls/Personal Protection.

8.1. Control parameters

P102: Keep out of reach of children.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P301+310: IF SWALLOWED: Immediately call a POISON CENTER or doctor.
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308+313: IF exposed or concerned: Get medical advice/attention.

8.2. Exposure controls

Appropriate Engineering Controls

Ensure there is sufficient ventilation of the area.
Local exhaust ventilation may be required in poorly ventilated areas.

Eye/Face Protection

Tightly fitting safety goggles. Ensure eye bath is to hand.

Skin Protection

Impermeable protective clothing.
Butyl gloves. Neoprene gloves. PVC gloves. Rubber gloves. Viton gloves.
Breakthrough time of the glove material > 4 hours.

Respiratory Protection

Self-contained breathing apparatus must be available in case of emergency.



Section 9. Physical and Chemical Properties.

9.1. Information on basic physical and chemical properties

The following information is not a technical specification or sales specification.

(a) Appearance:	Liquid, colourless to yellow.
(b) Odour:	Amine-like.
(c) Odour threshold;	No information available.
(d) pH:	8.5 - 11
(e) Melting point/freezing point;	No information available.
(f) Initial boiling point and boiling range;	> 200°C
(g) Flash point;	> 100°C
(h) Evaporation rate;	No information available.
(i) Flammability (solid, gas);	No information available.
(j) Upper/lower flammability or explosive limits;	No information available.
(k) Vapour pressure;	5 hPa @ 50°C
(l) Vapour density;	No information available.
(m) Relative density;	0.98
(n) Solubility(ies);	Not miscible.
(o) Partition coefficient: n-octanol/water;	No information available.
(p) Auto-ignition temperature;	No information available.
(q) Decomposition temperature;	No information available.
(r) Viscosity;	5500 mPas
(s) Explosive properties;	No information available.
(t) Oxidising properties.	No information available.

9.2 Other information

No information available.

Section 10. Stability and Reactivity.

10.1. Reactivity

Stable under recommended transport or storage conditions.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions will not occur under normal transport or storage conditions. Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Heat.

10.5. Incompatible materials

Strong oxidizing agents. Strong acids. Strong bases. Alcohols, acrylates, aldehydes, halogenated hydrocarbons, ketones, nitrites.

10.6. Hazardous decomposition products

Decomposition products can include and are not limited to: Ammonia, ethylenediamine, phenol, volatile amines and phenolics.



Section 11. Toxicological Information.

11.1. Information on toxicological effects

Relevant effects for mixture:

Effect	Route	Basis
Acute toxicity (harmful)	DRM ING	Hazardous: calculated
Corrosivity	OPT INH DRM	Hazardous: calculated
Sensitivity	DRM	Hazardous: calculated
Toxicity for reproduction	--	Hazardous: calculated

Opt - Optical

Inh - Inhalation

Drm - Dermal

Symptoms / routes of exposure

Skin contact:	Blistering may occur. Progressive ulceration will occur if treatment is not immediate.
Eye contact:	Corneal burns may occur. May cause permanent damage.
Ingestion:	Corrosive burns may appear around the lips. Blood may be vomited. There may be bleeding from the mouth or nose.
Inhalation:	There may be shortness of breath with a burning sensation in the throat. Exposure may cause coughing or wheezing.

Section 12. Ecological Information.

12.1. Toxicity	No information available.
12.2. Persistence and degradability	Not readily degradable.
12.3. Bioaccumulative potential	No information available.
12.4. Mobility in soil	No information available.
12.5. Results of PBT and vPvB assessment	This substance is not identified as a PBT substance.
12.6. Other adverse effects	
NONYLPHENOL -	Material is very toxic to aquatic organisms (LC50/EC50/IC50 below 1 mg/L in the most sensitive species).
2-PIPERAZIN-1-YLETHYLAMINE	Material is harmful to aquatic organisms (LC50/EC50/IC50 between 10 and 100 mg/L in the most sensitive species).

Section 13. Disposal Considerations.

13.1. Waste treatment methods

Dispose of in accordance with local authority regulations.



Section 14. Transport Information.

ADR. International Carriage of Dangerous Goods by Road.

14.1. UN number	UN 2922
14.2. Name and Description	Corrosive liquid, toxic, n.o.s.
14.3. Class	8
14.4. Packing group	II
14.5. Environmental hazards	Contents very toxic to aquatic organisms, may cause long term affects in the aquatic environment.
14.6. Special precautions for user	If exposed to contents, wear suitable protective clothing, gloves and eye / face protection.

IATA. International Air Transport Association.

14.1. UN number	UN 2922
14.2. UN Proper Shipping Name/Description	Corrosive liquid, toxic, n.o.s.
14.3. Class or Division	8 (6.1)
14.4. Packing group	II
14.5. Environmental hazards	Contents very toxic to aquatic organisms, may cause long term affects in the aquatic environment.
14.6. Special precautions for user	If exposed to contents, wear suitable protective clothing, gloves and eye / face protection.

IMDG. International Maritime Dangerous Goods.

14.1. UN number	UN 2922
14.2. UN proper shipping name	Corrosive liquid, toxic, n.o.s.
14.3. Class or Division	8
14.4. Packing group	II
14.5. Environmental hazards	Contents very toxic to aquatic organisms, may cause long term affects in the aquatic environment.
14.6. Special precautions for user	If exposed to contents, wear suitable protective clothing, gloves and eye / face protection.
14.7. Transport in bulk – Maritime only.	Bulk transport is not applicable to this product

Section 15. Regulatory Information.

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture
No information available.

15.2. Chemical safety assessment
No information available.



Section 16. Additional Information.

Full text of Phrases and Statements used in Section 3;

H302: Harmful if swallowed.

H312: Harmful in contact with skin.

H314: Causes severe skin burns and eye damage.

H317: May cause an allergic skin reaction.

H361: Suspected of damaging fertility or the unborn child.

H400: Very toxic to aquatic life.

H410: Very toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

The above information is believed to be accurate and represents the best information currently available.

No warranty is expressed or implied by the above information.

We assume no liability resulting from use of the above information.

The end user should conduct their own investigations to determine the suitability of the above information for their particular purpose.

Issue level	Date	Revisions
1	06/04/16	First issue.
2	20/03/17	Format Only.

End of Safety Data Sheet.