


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF OSPC TECHNOLOGY.

SPEC-F005.DWG

REVISONS		DWC NID SPEC-F005 * Effective 7/8/02 * DCP No. 1398	
DCP #	REV	DESCRIPTION	
XX	XX	XXXX	
XXXX	XXXX		



Features & Specifications:

- Overall length : 4 1/2" (115mm)
- Tips do not spread under pressure
- No contamination
- Non magnetic
- Static dissipative (106 – 109 DHM/SQ)

Applications

Ideal for handling semi-conductors, silicone chips, and delicate wafers. Static dissipative tweezers are ideal for use with sensitive components where ESD damage is a concern.



DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:		DRAWING TITLE:		Tweezers		ELECTRONIC FILE		REV	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.		DRAWN BY:	DATE:	SIZE	DWG. NO.	SCALE:	U.O.M.	SHEET:	OF
XXXX		XXXX	30-09-08	A	1353	NTS	INCHES [MM]	92N3634	XX
CHECKED BY:		DATE:	DATE:						
XXXX		30-09-08	30-09-08						
APPROVED BY:		DATE:	DATE:						
XXXX		30-09-08	30-09-08						