

Product type designation

SCALANCE XF204IRT

SCALANCE XF204IRT, FLAT, MANAGED IE IRT SWITCH, 4 X 10/100MBIT/S RJ45 PORTS, FAULT SIGNAL CONTACT WITH SET BUTTON, REDUNDANT POWER SUPPLY, PROFINET-IO DEVICE, NETWORK MANAGEMENT, RED.- MANAGER INTEGRATED, INCL. MANUAL ON CD, C-PLUG OPTIONAL



Transmission rate	
Transfer rate	10 Mbit/s, 100 Mbit/s
Interfaces	
Number of electrical/optical connections	
<ul style="list-style-type: none"> for network components or terminal equipment / maximum 	4
Number of electrical connections	
<ul style="list-style-type: none"> for network components or terminal equipment 	4
Type of electrical connection	
<ul style="list-style-type: none"> for network components or terminal equipment 	RJ45 port
Interfaces / for communication / integrated	
Number of 100 Mbit/s SC ports / for multimode	0
Number of 1000 Mbit/s LC ports / for multimode	0
Interfaces / others	
Number of electrical connections	
<ul style="list-style-type: none"> for signaling contact 	1
<ul style="list-style-type: none"> for power supply 	1
<ul style="list-style-type: none"> for redundant voltage supply 	1
Type of electrical connection	
<ul style="list-style-type: none"> for signaling contact 	2-pole terminal block
<ul style="list-style-type: none"> for power supply 	4-pole terminal block
design of the removable storage	
<ul style="list-style-type: none"> C-PLUG 	Yes

Signal-Inputs/outputs	
Operating voltage / of the signaling contacts	
<ul style="list-style-type: none"> • for DC / Rated value 	24 V
Operating current / of the signaling contacts	
<ul style="list-style-type: none"> • for DC / maximum 	0.1 A
Supply voltage, current consumption, power loss	
Type of voltage / of the supply voltage	DC
Supply voltage	
<ul style="list-style-type: none"> • external 	24 V
<ul style="list-style-type: none"> • external 	18 ... 32 V
Product component / fusing at power supply input	Yes
Fuse protection type / at input for supply voltage	0.6 A / 60 V
Consumed current / maximum	0.2 A
Active power loss	
<ul style="list-style-type: none"> • for DC / at 24 V 	4.8 W
Permitted ambient conditions	
Ambient temperature	
<ul style="list-style-type: none"> • during operation 	-40 ... +60 °C
<ul style="list-style-type: none"> • during storage 	-40 ... +60 °C
<ul style="list-style-type: none"> • during transport 	-40 ... +60 °C
<ul style="list-style-type: none"> • Note 	If the IE switch XF 200 is installed horizontally a maximum ambient temperature of +40 °C is permitted
Relative humidity	
<ul style="list-style-type: none"> • at 25 °C / without condensation / during operation / maximum 	95 %
Protection class IP	IP20
Design, dimensions and weight	
Design	Flat
Width	75 mm
Height	125 mm
Depth	73 mm
Net weight	0.25 kg
Mounting type	
<ul style="list-style-type: none"> • 35 mm DIN rail mounting 	Yes
<ul style="list-style-type: none"> • wall mounting 	No
<ul style="list-style-type: none"> • S7-300 rail mounting 	No
<ul style="list-style-type: none"> • S7-1500 rail mounting 	No
Product properties, functions, components / general	
Cascading in the case of a redundant ring / at reconfiguration time of $<\sim 0.3\sim$ s	50
Cascading in cases of star topology	Any (depending only on signal propagation time)

Product functions / management, configuration

Product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• Configuration with STEP 7	Yes
• Port mirroring	No
• multiport mirroring	No
• with IRT / PROFINET IO switch	Yes
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
Protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	No
• DCP	Yes
• LLDP	Yes
Identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 – higher-level designation/location designation	Yes
Protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes

Product functions / Diagnosis

Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes
• Error statistics	Yes

Product functions / DHCP

Product function	
• DHCP client	Yes

Product functions / Redundancy

Product function	
------------------	--

• Ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• Media Redundancy Protocol for Planned Duplication (MRPD)	Yes
• Passive listening	Yes

Product functions / Security

Protocol / is supported	
• SSH	Yes

Product functions / Time

Product function	
• SICLOCK support	Yes
Protocol / is supported	
• NTP	No
• SNTP	Yes

Standards, specifications, approvals

Standard	
• for FM	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4
• for hazardous zone	EN 60079-0: 2006, EN60079-15: 2005, II 3 G Ex nA II T4, KEMA 07 ATEX 0145 X
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1
• for hazardous zone / from CSA and UL	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4
• for emitted interference	EN 61000-6-4:2001 (Class A)
• for interference immunity	EN 61000-6-4:2001
Certificate of suitability	EN 61000-6-4:2001
• CE marking	Yes
• C-Tick	Yes
• KC approval	No
• Railway application in accordance with EN 50155	No
• Railway application in accordance with EN 50124-1	No

Marine classification association	
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) • Bureau Veritas (BV) • Det Norske Veritas (DNV) • Germanische Lloyd (GL) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS) 	No
MTBF / at 40 °C	80.58 y

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> • to website: Selector SIMATIC NET SELECTION TOOL • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAx Download Manager • to website: Industry Online Support 	http://www.siemens.com/snst http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/automation/net/catalog http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

Security information

Security information	<p>Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit http://www.siemens.com/industrialsecurity. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit http://support.automation.siemens.com. (V3.4)</p>
----------------------	--

last modified:

05.03.2015