

## Cemented carbide T-groove cutter

**ORION**<sup>®</sup>

### Application:

For making T-slots conforming to DIN 650

### Execution:

- Straight shank according to DIN 1835 A
- Stable cemented carbide cutters
- Cross-toothing
- Corners 0.3 mm x 45°, chamfered
- In accordance with DIN 650



<b>Art. no.</b>	<b>16525 140</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	16525140
<b>Cutting material</b>	Carbide
<b>Surface</b>	Uncoated
<b>Type</b>	N
<b>Number of cutting edges</b>	6 PCS
<b>Tool holding device</b>	HA parallel shank
<b>Cutting edge diameter</b>	25 mm
<b>Width of cutting edge</b>	11 mm
<b>Suitable for T-groove</b>	14 mm
<b>Length</b>	80 mm
<b>Neck diameter</b>	12 mm
<b>Shank diameter</b>	16 mm
<b>fz steel 1000</b>	0.035 mm
<b>Gross Weight</b>	0.100 kg
<b>Product Group</b>	165

### EAN

4039247104093