

SDUC offset cemented carbide boring bar, positive, right

for longitudinal and copy turning with DC indexable insert with holder

ATORN[®]



Application

For longitudinal and copy turning with DC indexable insert, 55°

Version

- precision-manufactured **solid carbide** boring bar, with inner cooling, D type, 93.5° pitch angle, 55° tip angle, 7° clearance angle

Advantage

- slim contour, optimised for copy turning work
- Positive body geometry ensures low cutting forces

Art. No.	17827 688
ISO name	E0408-SDUC R/L 04-AX
Min. bore diameter	5.6 mm
Shaft diameter	8 mm
Clearance length	26 mm
Length	57 mm
Programming size	3 mm
Plate height	1.5 mm
Suitable for indexable inserts	DC.. 04..
Tool design	Left

EAN-Code

4050293692457