

## Prima drill chuck

Heavy-duty industrial version



### Application:

For holding tools with straight shank.

### Execution:

- Hardened body head with keyholes and jaws.
- Keyed drill chuck, DIN ISO 10887.

### Advantage:

- High clamping force thanks to toothed ring.
- Very strong and resistant to wear.

### Delivery:

1x 0.5-6.5 mm/B 12 drill chuck.



<b>Art. no.</b>	<b>21290 170</b>
<b>Brand</b>	RÖHM
<b>Manufacturer Part Number</b>	72825
<b>Min./max. clamping width</b>	1-16 mm
<b>Suitable for taper</b>	B 18
<b>Outer diameter</b>	56.5 mm
<b>Gross Weight</b>	0.931 kg
<b>Product Group</b>	201

### EAN

4019208018201