

SG-P11-070-010-12-HH-782X-00000

PLANETARY GEARBOXES

SG 070

$i=010$


$\varphi=12'$

MADE IN ITALY

IP64




Dimensions (Units:mm)



MODEL	Rated output torque [Nm]	Maximum acceleration output torque [Nm]	Emergency step output torque [Nm]	Backlash [arcmin]	Nominal input speed [min ⁻¹]	Maximum momentary input speed [min ⁻¹]	Torsional stiffness [Nm/arcmin]	Maximum radial force applying on output shaft [N]	Maximum axial force applying on output shaft [N]	Gear efficiency [%]	Gear moment of inertia [Kg ^m ²]
SG-P11-070-010-12-HH-782X-00000	18	30	60	12'	4000	6000	3	1300	1400	97	0.06x10 ⁻⁴

Suggested motors



103-H7823 SERIES



MOUNTING OPERATION MODE: ■ Tightening torque M=5 Nm ■ Locking bolt M4 ■ R.T.A. Quality Control