

Test pump HP 300, 0 to 60 bar

With 30-L oval container



Application:

For hydrostatic testing of parts such as fittings, pipes, pipelines, tanks, gas bottles, test stands and many other high-pressure components.

Execution:

- Test media: clear water, water/oil emulsion, hydraulic oil or low viscosity oil
- With drain valve, pressure gauge and hot-dip galvanised container



Art. no.	56377 005
Brand	URACA
Manufacturer Part Number	W2851-K1 +ZUBEHÖR
Model	HP 300
Bin capacity	30 l
Min./max. pressure	0-60 bar
Design	Stationary
Connection thread	G 1/2 inch
Form	Oval
Feed volume per stroke	28 cm ³
Length x width x height	430 x 310 x 330 mm
Material	Sheet steel
Weight	14 kg
Gross Weight	14.000 kg
Product Group	575