

## Micrometer

Tips made of carbide or carbide-tipped

Mitutoyo

### Application:

For measuring grooves, distances etc.

### Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Tips made of carbide or carbide-tipped, measuring tip radius 0.3 mm
- Friction coupling for consistent, repeatable measuring force
- Anvil and spindle end with two angles (15° and 30°) and small radii as contact points

### Advantage:

- Accesses hard-to-reach measuring points

### Delivery:

Includes box, setting standard (from 25 mm), adjustment wrench



<b>Art. no.</b>	<b>32016 734</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	112-213
<b>Min./max. length measuring range</b>	0-25 mm
<b>Vernier scale</b>	0.01 mm
<b>Measuring surface depth</b>	10 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Bracket depth</b>	38 mm
<b>Spindle clamping</b>	Yes
<b>Angle of the tip</b>	30 Degree
<b>Error limit</b>	3 µm
<b>Display</b>	Nonius
<b>Type</b>	Carbide tip
<b>Min./max. measurement force</b>	3-8 N
<b>Calibration Group</b>	D
<b>Gross Weight</b>	0.300 kg
<b>Product Group</b>	3MA

### EAN

4946368009513