

# NTC - Surface sensor

with square sensor 8x8 mm and cross hole



## Application:

The surface temperature sensor is provided with a cross hole on the sensor (square 8x8 mm) and can be screwed tightly, for example, using a screw at the destination during continuous measurements.

## Execution:

- Sensor type: NTC
- Measuring range: -50 to +80°C
- Accuracy: ±0.2°C at 0 to +70°C
- Response time: 150 s
- Sensor shape: Square 8x8 mm
- Length of probe/sensor tube tip: 40 mm

Art. no.	46108 325
Brand	TESTO
Manufacturer Part Number	0628 7516
Sensor type	NTC
Probe type	Surface probe
Min./max. temperature measuring range	-50 to 80 °C
Accuracy temperature	+/- 0.2°C at 0 to +70°C
Response time sensor	150 s
Length sensor tube tip	40 mm
Cable length	2 m
Gross Weight	0.100 kg
Product Group	4CF



## EAN

4029547006814