

## Torque screwdriver set ESD, adjustable 0.4–1.0 Nm

TorqueVario S-ESD, 13 pieces



### Application:

Electrostatically dissipative tools protect electronic components

### Execution:

- Continuously adjustable torque with mil adjustment tool included in the set
- Ergonomic multi-component handle made of electrostatically dissipating plastic
- Standards: IEC 6134-5-1/DIN EN ISO 6789
- With ESD universal bit retention blade, 1/4 inch

### Delivery:

In stable box with foam insert incl. Factory inspection log



<b>Art. no.</b>	<b>52206 990</b>
<b>Brand</b>	WIHA
<b>Manufacturer Part Number</b>	43898
<b>Composition of set</b>	Slotted 4.5 x 0.5 and 4.5 x 0.6 mm
<b>Tip size</b>	PH0, PH1, PZ0, PZ1, TX7, TX8, TX9, TX10
<b>Blade length</b>	146 mm
<b>Material of handle</b>	2-component plastic
<b>Error limit (%)</b>	6 %
<b>Min./max. torque</b>	0.4-1 Nm
<b>Calibration certificate</b>	Yes
<b>Scale value</b>	0.1
<b>Handle length</b>	127 mm
<b>Gross Weight</b>	0.671 kg
<b>Product Group</b>	537

### EAN

4010995438982