

SMT WLAN Passive Patch Antenna

- **SMT Mount**
- **2487MHz (standard)**
- **High Performance**
- **25x25x4 mm**
- **Suitable for embedded applications**




ADA-WLAN25254 is a high performance, high quality passive WLAN antenna module for SMT mount with standard reflow soldering.


It's especially designed for small integrated devices and low cost production creating high yield.

Specification


Category	GPS
Frequency	2450MHz \pm 50 MHz
Center Frequency	2487MHz \pm 4MHz
Polarization	R.H.C.P.
Bandwidth	80 MHz min Return Loss \square -10dB
VSWR	1.5 Max
Gain at Zenith	Typ. 5.0 dBi
Axel Ration	3 dB Max
Impedance	50 Ω
Freq. Temp. Coeff.	0 \pm 20ppm / \square
Operating temperature	-40 — +105 ° C
Size	25 x 25 x 4 mm
Weight	5 \pm 0.5 grams
Mounting	SMT
ROHS	Compliant with EU




Dimensions



Layout Dimensions



Ground Plane Dimension



Ordering codes

TYPE	Description	Comment
ADA-WLAN25254	WLAN Patch	WLAN Ceramic Patch

For the latest updates, visit our Web site: www.adactus.se

Disclaimer

Information furnished is believed to be accurate and reliable. However, Adactus assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. Adactus reserves the right to make changes without further notice to any product herein to improve reliability, function or design. Adactus does not assume any liability arising out of the application or use of any product described herein. This publication supersedes and replaces all information previously supplied. Adactus products are not authorized as critical components in life support devices or systems.