

Data sheet



Type: PVC-stranded wire
Brief description: LiYv
Dimension: 0,25 qmm

Construction:

Conductor tinned stranded copper wire 14x0,15 mm
O.D. ca. 1,3 mm
Insulation PVC acc. to VDE 0207

Technical characteristics:

Insulation resistance min. 200M Ω x km at +20°C
Operating voltage max. 900V
Testing voltage 2500V
Temperature range static: -30°C to +70°C
dynamic: -5°C to +70°C
Bending radius static: min. 10 x O.D.
dynamic: min. 12 x O.D.

Colours available from stock:

Brown-red, yellow-pink, green-red, green-black, pink-black, red-blue, red-black, white-blue, white-brown, white-yellow, white-green, white-grey, white-pink, white-red, white-black, white-vio

Produktgruppe: Elektronik-Industrie	Ersteller: SF	Geprüft: WK
RoHS-konform, EG-Richtlinie: 2002/95/EG: ja	Art.-Nr.: 0601025	
RoHS-konform, EG-Richtlinie: 2011/65/EU: ja	Stand: 01/09	
	Version: 1.1	
Technische Änderungen und Irrtümer vorbehalten.	Seite 1 von 1	