

Ascent 100 II Arch 160

ASCENT 100 II ARCH 3700 4K STD EMG 160
2060576



Product features

- The ASCENT 100 II ARCH 3700 4K STD EMG 160 is a high efficient non dimmable downlight luminaire with 3 hour emergency, Colour rendering index Ra >80, Colour temperature: 4000K Neutral White, Class II, Protection rating IP40/IP20, Cut out dimensions: 178mm. Additional accessories of diffusers and plaster in available.



PRODUCT OVERVIEW

Product name	ASCENT 100 II ARCH 3700 4K STD EMG 160
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Ceiling recessed mounting
General application	Hospitality, Office, Retail
ETIM Class	EC001744
Warranty	5 years
Fixture luminous flux (lm)	3766
Luminaire efficacy (lm/W)	118
LOR (%)	100
Colour temperature (K)	4000
CRI (Ra)	80
Colour Consistency (SDCM)	3
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	85
Glare control	< 26
Photobiological Risk Group	RG0
Total power consumption (W)	32
Electrical protection	Class II
Control gear type	Electronic ballast
Control gear mounting	Remote
Dimmable	No
Dimming method	N/A
Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP40/20
IK rating	IK02
Product EAN number	5025768605767

DATA TABLE

Ascent 100 II Arch 160

ASCENT 100 II ARCH 3700 4K STD EMG 160
2060576

General data

Product name	ASCENT 100 II ARCH 3700 4K STD EMG 160
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Ceiling recessed mounting
General application	Hospitality, Office, Retail
Operating temperature range (°C)	25°C...+25°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
Warranty	5 years

Optical data

Fixture luminous flux (lm)	3766
Luminaire efficacy (lm/W)	118
LOR (%)	100
Colour temperature (K)	4000
CRI (Ra)	80
Colour Consistency (SDCM)	3
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	85
Distribution type	Diffuse
Glare control	< 26
Photobiological Risk Group	RG0
Emergency duration (h)	3

Electrical data

Total power consumption (W)	32
Mains voltage (V)	220-240V
Lamp power factor	0.95
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	15
Electrical protection	Class II
Control gear required	Yes
Control gear type	Electronic ballast
Control gear mounting	Remote
Transformer required	No
Dimmable	No
Dimming method	N/A
Drive current (mA)	600
Inrush Current (A)	25
Inrush Duration (µs)	150
Glow Wire Test (°C)	650
Energy Efficiency Class (A->G) of contained light source	C
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	24
Max. Luminaires per 13A C Breaker	32
Max. Luminaires per 16A C Breaker	40

Ascent 100 II Arch 160

ASCENT 100 II ARCH 3700 4K STD EMG 160

2060576

Max. Luminaires per 20A C Breaker	51
Max. Luminaires per 10A B Breaker	14
Max. Luminaires per 13A B Breaker	19
Max. Luminaires per 16A B Breaker	24
Max. Luminaires per 20A B Breaker	30

Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	47000

Physical data

Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP40/20
IK rating	IK02
Diffuser finish	Opal
Diffuser material	PMMA Acrylic
Reflector finish	High-gloss
Nominal Product Height (mm)	94
Nominal Product Diameter (mm)	189
Cutout Dimensions (W x L in mm or Diameter in mm)	178
Weight (kg)	1.92

Packaging

Single packaging type	Carton
Product EAN number	5025768605767
Packaging single length / height (cm)	30.0
Packaging single width (cm)	30.0
Packaging single depth (cm)	12.5
DUN14 (outer)	05025768605767
Units per outer package	1
Packaging outer length / height (cm)	30.0
Packaging outer width (cm)	30.0
Packaging outer depth (cm)	12.5





Safety data

Optimal operating condition (°C)	25-25
----------------------------------	-------

PHOTOMETRY

Ascent 100 II Arch 160

ASCENT 100 II ARCH 3700 4K STD EMG 160
2060576



TECHNICAL DRAWINGS

