

Felt polishing and grinding points

Shank diameter 6 mm



Application:

For pre-polishing and gloss polishing of injection moulding tools, fittings, cemented carbide cutting knives and for gloss polishing of stainless steel components (INOX).

Advantage:

- Exact preservation of geometric shapes due to its hardness
- Freely profilable and can therefore also be used for tools with complicated geometries
- Exact preservation of geometric shapes due to its hardness



Art. no.	69202 015
Brand	PFERD
Manufacturer Part Number	4007220153802
Form	Cylindrical
Head diameter x head length	20 x 25 mm
Min./max. recommended rotation speed	5000-10000 rpm
Max. rotation speed	30500 rpm
Number of pieces per packet	10 PCS
Gross Weight	0.018 kg
Product Group	6AB

EAN

4007220153802