

MATERIAL

Black-oxide steel, class 10 (tensile strength 1000 N/mm²).



BALL AND SPRING

Stainless steel.

FEATURES AND APPLICATIONS

GN 508.2 T-nuts have the same dimension of DIN 508.

The device provided with a ball and spring and located inside the dowel allows it to slide avoiding accidental vertical slipping. These dowels are highly recommended for use with fixing hinges for aluminium sections type CFG. (see page 1360).



Code	Description	a-0.3-0.5	d	e	h	k	s	Groove width DIN 650	⚖
GN.24801	GN 508.2-10-M8-10	10	M8	15	12	6	0.65	10	14
GN.24805	GN 508.2-12-M10-10	12	M10	18	14	7	0.65	12	22
GN.24811	GN 508.2-14-M12-10	14	M12	22	16	8	1	14	34
GN.24815	GN 508.2-18-M16-10	18	M16	28	20	10	1	18	68
GN.24821	GN 508.2-22-M20-10	22	M20	35	28	14	1.6	22	155

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18